

Wheels

 120 - 1500 kg

Rubber wheel

Tread

Black elastic tyre

Wheel body

Cast iron

Bearing

Ball bearing



								
mm	mm	kg	mm	mm				
100	38	150	20	41				B81.100
100	50	210	20	60				B81.101
125	50	275	20	60				B81.127
150	50	350	25	60				B81.151
200	50	450	25	60				B81.202
200	75	550	30	82				B81.203
200	100	675	40	108				B81.204
250	50	500	25	60				B81.252
250	75	750	30	82				B81.253
300	75	850	30	82				B81.303
400	75	1200	30	82				B81.400
400	100	1500	40	108				B81.401

Polyurethane wheel

Tread

Cast polyurethane
95+/-3 Shore A

Wheel body

Aluminium

Bearing

Ball bearing



80	20	120	12	20				B90.080
80	40	250	15	40				B90.081
100	30	200	15	40				B90.100
100	40	280	15	40				B90.101
100	40	200	20	40				B90.102
125	30	250	15	40				B90.125
125	38	300	20	41				B90.127
125	50	450	20	60				B90.126
150	40	400	20	50				B90.150
150	50	550	20	60				B90.152
160	50	600	20	60				B90.160
180	50	700	20	60				B90.180
200	50	800	20	60				B90.200
225	60	1000	20	70				B90.225
250	50	1000	20	60				B90.251

Polyurethane wheel

Tread

Cast polyurethane
78 Shore A

Wheel body

Aluminium

Bearing

Ball bearing



100	30	150	12	40				B91.100
125	40	225	15	40				B91.125
160	50	500	20	60				B91.160
200	50	700	20	60				B91.200