



Compact castors



BS ROLLEN®
we are moving everything

								
mm	mm	kg	mm	mm	mm	mm	mm	mm
35	25	100	58	60x60	48x48/38x38	7	20	A600.C10.035
35	25	100	58	60x60	48x48/38x38	7	20	A620.C10.035

 **100 kg**



Swivel castor

Sheet steel fork,
dual-row ball collar
in fork head

Tread

Polyurethane
90+/- 3 Shore A

Wheel body

Steel

Bearing

Ball bearing



Swivel castor with brake

Sheet steel fork,
dual-row ball collar
in fork head

Tread

Polyurethane
90+/- 3 Shore A

Wheel body

Steel

Bearing

Ball bearing

								
mm	mm	kg	mm	mm	mm	mm	mm	mm
35	25	100	58	11	20			A601.C10.035
35	25	100	58	11	20			A621.C10.035



Swivel castor

Sheet steel fork,
dual-row ball collar
in fork head

Tread

Polyurethane
90+/- 3 Shore A

Wheel body

Steel

Bearing

Ball bearing



Swivel castor with brake

Sheet steel fork,
dual-row ball collar
in fork head

Tread

Polyurethane
90+/- 3 Shore A

Wheel body

Steel

Bearing

Ball bearing