

Heavy-duty castors



BS ROLLEN®
we are moving everything



Description

Welded steel housing
zinc-plated
ball bearing in fork head

Model

- Swivel castor
- Fixed castor
- Swivel castor with wheel-/total brake

mm	mm	kg	mm	mm	mm	mm	mm	mm	mm	mm	mm

100	40	150	150	100x85	80x60	10	35	RR100.B80.100	RR110.B80.100	RR120.B80.100
100	40	150	150	138x110	105x75/80	11	35	RR100.B80.101	RR110.B80.101	RR120.B80.101
125	50	200	170	138x110	105x75/80	11	50	RR100.B80.125	RR110.B80.125	RR120.B80.125
160	50	350	200	138x110	105x75/80	11	60	RR100.B80.160	RR110.B80.160	RR120.B80.160
200	50	450	245	138x110	105x75/80	11	60	RR100.B80.200	RR110.B80.200	RR120.B80.200
250	50	550	295	138x110	105x75/80	11	70	RR100.B80.250	RR110.B80.250	RR120.B80.250
250	63	580	315	175x140	140x105	14	75	RR100.B80.251	RR110.B80.251	RR120.B80.251
300	60	700	365	175x140	140x105	14	75	RR100.B80.300	RR110.B80.300	RR120.B80.300

100	40	150	150	100x85	80x60	10	35	RR100.B83.100	RR110.B83.100	RR120.B83.100
100	40	150	150	138x110	105x75/80	11	35	RR100.B83.101	RR110.B83.101	RR120.B83.101
125	50	200	170	138x110	105x75/80	11	50	RR100.B83.125	RR110.B83.125	RR120.B83.125
160	50	350	200	138x110	105x75/80	11	60	RR100.B83.160	RR110.B83.160	RR120.B83.160
200	50	450	245	138x110	105x75/80	11	60	RR100.B83.200	RR110.B83.200	RR120.B83.200

100	38	150	145	100x85	80x60	10	35	RR100.B81.100	RR110.B81.100	RR120.B81.100
100	50	210	150	138x110	105x75/80	11	35	RR100.B81.101	RR110.B81.101	RR120.B81.101
125	50	275	170	138x110	105x75/80	11	50	RR100.B81.125	RR110.B81.125	RR120.B81.125
150	50	350	195	138x110	105x75/80	11	60	RR100.B81.150	RR110.B81.150	RR120.B81.150
150	50	350	212	175x140	140x105	12	55	RR100.B81.151	RR110.B81.151	RR120.B81.151
150	75	425	212	200x160	160x120	16	61	RR100.B81.152	RR110.B81.152	RR120.B81.152
200	50	450	245	138x110	105x75/80	11	60	RR100.B81.200	RR110.B81.200	RR120.B81.200
200	50	450	264	175x140	140x105	12	67	RR100.B81.201	RR110.B81.201	RR120.B81.201
200	75	550	264	200x160	160x120	16	65	RR100.B81.202	RR110.B81.202	RR120.B81.202
200	100	675	280	255x200	210x160	16	65	RR100.B81.203	RR110.B81.203	RR120.B81.203
250	50	500	295	138x110	105x75/80	11	70	RR100.B81.250	RR110.B81.250	RR120.B81.250
250	75	750	315	175x140	140x105	14	75	RR100.B81.251	RR110.B81.251	RR120.B81.251
250	75	750	314	200x160	160x120	16	80	RR100.B81.252	RR110.B81.252	RR120.B81.252
300	75	850	365	175x140	140x105	14	75	RR100.B81.300	RR110.B81.300	RR120.B81.300
300	75	850	375	200x160	160x120	16	75	RR100.B81.301	RR110.B81.301	RR120.B81.301
400	75	1200	475	200x160	160x120	16	70	RR100.B81.400	RR110.B81.400	RR120.B81.400
400	100	1500	495	255x200	210x160	16	85	RR100.B81.401	RR110.B81.401	RR120.B81.401

150 - 1500 kg



Tread
Black elastic tyre

Wheel body
Aluminium

Bearing
Ball bearing



Tread
Grey elastic tyre

Wheel body
Aluminium

Bearing
Ball bearing



Tread
Black elastic tyre

Wheel body
Cast iron

Bearing
Ball bearing