



EDDELSTAHL®
Rostfrei
Inox
Stainless
Steel

- 4 Type (Base plate)**
- D0** fine turned, without rubber underlay
 - D1** fine turned, with rubber underlay, inlaid, black

d ₁	d ₂	l ₁					l ₂					l ₃ ≈					l ₇	k			
		Version S / SK					Version T / TK and U / UK					Version V / VK							Version W		
80	M 8	8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	34	54,5
80	M 10	10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	37	54,5
80	M 12	12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	40	54,5
80	M 16	-	-	-	-	-	75	100	125	150	200	75	100	125	150	118	143	168	193	46	54,5
80	M 20	-	-	-	-	-	75	100	125	150	200	100	125	150	200	143	168	193	243	54	54,5
80	M 24	-	-	-	-	-	100	125	150	200	-	100	150	200	-	168	218	268	-	-	54,5
100	M 8	8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	35	70,5
100	M 10	10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	38	70,5
100	M 12	12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	41	70,5
100	M 16	-	-	-	-	-	75	100	125	150	200	75	100	125	150	119	144	169	194	47	70,5
100	M 20	-	-	-	-	-	75	100	125	150	200	100	125	150	200	144	169	194	244	55	70,5
100	M 24	-	-	-	-	-	100	125	150	200	-	100	150	200	-	169	219	269	-	-	70,5
120	M 20	-	-	-	-	-	75	100	125	150	200	-	-	-	-	-	-	-	-	59	95,5
120	M 24	-	-	-	-	-	100	125	150	200	-	-	-	-	-	-	-	-	-	-	95,5
120	M 30	-	-	-	-	-	100	125	150	200	-	-	-	-	-	-	-	-	-	-	95,5

Specification

- Base plate
Stainless Steel AISI 304
- Threaded stem
Stainless Steel AISI 303
- Hexagon nut ISO 4032
Stainless Steel AISI 304
- Rubber underlay, inlaid
Perbunan® (NBR), 70 Shore A
- *Stainless Steel characteristics* → Page 1489
- *Elastomer characteristics* → Page 1483
- *Load rating information* → Page 1475
- **RoHS compliant**

Information

Stainless Steel-Levelling feet GN 21 / GN 23 will be delivered mounted and are not removable.

see also...

- *Stainless Steel-Levelling feet GN 31* → Page 1046
- *Stainless Steel-Levelling feet GN 41* → Page 1042

How to order (without mounting holes)

1	d ₁
2	d ₂
3	l ₇ (l ₁ , l ₂ , l ₃)
4	Type (Base plate)
5	Version (Stem)

GN 21-100-M20-55-D1-X

How to order (with mounting holes)

1	d ₁
2	d ₂
3	l ₇ (l ₁ , l ₂ , l ₃ , l ₇)
4	Type (Base plate)
5	Version (Stem)

GN 23-80-M10-50-D0-S