



**2**

Latch distance <b>A</b>														
6	10	14	18	20	22	24	26	28	30	34	38	40	50	

**3**

Specification	
• Lock housing Stainless Steel AISI 303	<b>NI</b>
• Latch Stainless Steel AISI 304	
• Protection class IP 65	
• <i>Stainless Steel characteristics</i> → Page 1489	
• <i>RoHS compliant</i>	

Accessories
• Socket keys GN 119.2 → Page 940
• Protective caps GN 120 → Page 942
• Opening handles GN 120.1 → Page 943

Information
Stainless Steel-Latches GN 115 lock by a turning operation limited to 90° which moves the locking behind the door frame. The bevels of the locking ease the closing of the door.
Latches with different cranks cover a latch distance A from 6 to 28 mm.
The operating bolt is fitted with an O-ring for sealing.
Stainless Steel-Latches GN 115 are supplied with loosely enclosed latch.
see also...
• <i>Construction and assembly instructions</i> → Page 897
• <i>List of latch types</i> → Page 892 ff.
• <i>Stainless Steel-Latches GN 115 (lockable)</i> → Page 902
• <i>Latches GN 115 (operation with key)</i> → Page 898
• <i>IP-Protection classes</i> → Page 1482

How to order	
<b>GN 115-DK-18-NI</b>	<b>1</b> Type
	<b>2</b> Latch distance A
	<b>3</b> Material