



RODELSTAHL®
Rost
frei
Inox
Stainless
Steel

1

$d_1^{+0,2}_{-0,3}$	$d_2 - 0,5$	h	t	for serrated locking plates GN 187.4 - d_1
22	26	14,5	12,5	22
27	31	16,5	14,5	27
32	36	19,5	17,5	32
40	44	24,5	22,5	40

Specification

- Steel **ST**
- blackened
- Stainless Steel AISI 303 **NI**
- Stainless Steel characteristics → Page 1489
- RoHS compliant

2

Information

- see also...
- Serrated locking plates GN 187.4 → Page 824

How to order
GN 187.1-27-NI

1	d_1
2	Material