



3 Type

- A** Ball knob DIN 319
- D** Domed gear knob GN 719
- E** Cylindrical knob GN 519

d₁	l₁			d₂	d₃	d₅	d₆	l₂	l₃	l₅	l₆
8	63	80	100	M 6	20	20	18	9	18	32	40
10	80	100	125	M 8	25	26	21	11	22,5	42	50
12	100	125	160	M 10	32	33	23	14	29	55	65
14	125	160	200	M 12	35	33	26	16	32,5	55	80
16	160	200	250	M 14	40	38	28	18	37	69	90

Specification

- Shafts
 - Steel **ZB**
zinc plated, blue passivated
 - Stainless Steel AISI 303 **NI**
matt shot-blasted
- Knobs
 - Plastic
 - Duroplast (Phenolic PF)
 - black, shiny finish
 - screwed on
- *Ball knobs DIN 319* → Page 33
- *Domed gear knobs GN 719.2* → Page 36
- *Cylindrical knobs GN 519* → Page 39
- *Stainless Steel characteristics* → Page 1144
- *Plastic characteristics* → Page 1141
- **RoHS compliant**

How to order (Steel)

GN310-10-125-E-ZB

1	d₁
2	l₁
3	Type
4	Finish

How to order (Stainless Steel)

GN310-12-100-A-NI

1	d₁
2	l₁
3	Type
4	Material