



3 Type

- A** with male thread
- B** with female thread



d_1	d_2	d_3	l_1	$l_2 \pm 1$	$l_3 \pm 1$	A/F	t min.
25	M 6	10	11	37,5	15	8	10
32	M 8	13	13	48	19	10	12
40	M 10	16	14	61	24	14	16
50	M 12	20	21	78	31	17	16

Specification

- Plastic
Duroplast (Phenolic PF)
- temperature resistant up to 110 °C
- black, shiny finish

GN 319.2

Shaft steel
zinc plated, blue passivated

GN 319.5

Shaft
Stainless Steel AISI 303
matte shot-blasted

• *Stainless Steel characteristics* → Page 1489

• *Plastic characteristics* → Page 1483

• **RoHS-compliant**

Information

Revolving ball knobs GN 319.2 / GN 319.5 can be utilized instead of revolving handles i. e. with handwheels.

How to order (Steel)

GN319.2-32-M8-A

- 1 d_1
- 2 d_2
- 3 Type

How to order (Stainless Steel)

GN319.5-25-M6-B

- 1 d_1
- 2 d_2
- 3 Type