



ROSTFREI
Inox
Stainless
Steel

1 2

d ₁	I ₁ Nominal length						I ₂ MS-pad	KU-pad	d ₂ MS-pad	KU-pad	d ₃	d ₄	d ₅	h	k
	M 5	10	15	20	25	-									
M 5	10	15	20	25	-	0,5	1	3	3	19	9	12	14	8	
M 6	10	16	20	25	30	1	1,3	4	3,5	24	12	14	16,5	9,5	
M 8	20	25	30	40	-	1,5	1,6	6	5	30	14	16	19,5	11	
M 10	20	25	30	45	55	2	1,9	8	6,5	36	16	18	22,5	12,5	

Specification

- Plastic Technopolymer (Polyamide PA) black shiny finish
- Threaded bolt Stainless Steel AISI 304 Cu
- Pivot
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- *Stainless Steel characteristics* → Page 1144
- *Plastic characteristics* → Page 1141
- **RoHS compliant**

3

Information

Knurled screws GN 421.10 with pads in brass or plastic are used in applications, where marks and damage on the workpiece are unacceptable.

see also...

- *Star knobs GN 6336.10 (with brass / plastic thrust pad)* → Page 282
- *Grub screws GN 913.3 (with brass / plastic thrust pad)* → Page 520
- *Stainless Steel-Grub screws GN 913.5 (with brass / plastic thrust pad)* → Page 521

How to order

GN 421.10-M8-25-MS

1	d ₁
2	I ₁
3	Material thrust pad

1.1
1.2
1.3
1.4
1.5
1.6
1.7
1.8
1.9