



d <sub>1</sub>				Length l ±0,5						d <sub>2</sub>	d <sub>3</sub>	h	r	t min.	
	NI	A4	AL												
6	-	-		32	45	55	64	88	-	-	M 3	9	26	7	7
8	-	8		55*	64	88*	96	100	120*	128	M 4	12	35	10	8
10	10	10		88*	100	120*	180	200	235*	-	M 5	15	43	12	12
12	-	12		125	160	200	250	-	-	-	M 6	-	51	14	12
16	-	16		160	200	250	300	-	-	-	M 6	-	59	18	12

\* suitable for 19" rack and enclosure layout

Specification

- Stainless Steel** NI
  - AISI 303 (A2) for d<sub>1</sub> = 8, 10
  - AISI 304 (A2) for d<sub>1</sub> = 12, 16
  - matt shot-blasted GS
  - electropolished EP
- Stainless Steel** A4
  - AISI 316L GS
  - matt shot-blasted
- Aluminum** AL
  - plastic coated
  - black, RAL 9005, textured finish ● SW
  - silver, RAL 9006, textured finish ● SR
  - red, RAL 3000, textured finish ● RS
  - anodized, natural color ● EL
- Location discs**
  - Stainless Steel, AISI 303 (for NI and AL)
  - Stainless Steel, AISI 316L (for A4)

• *Stainless Steel characteristics* → Page 1489

• *Load rating information* → Page 1452

• **RoHS compliant**

On request

- Stainless Steel version A4 electropolished

Information

Stainless Steel-Cabinet „U“ handles GN 425 Ø 6, Ø 8 and Ø 10 are supplied with two stainless steel location discs. They guarantee a perfect location even with large holes in the cabinet. The discs are loosely enclosed.

The manufacturing process (bending) allows the production of **special lengths** in relatively small quantities.

see also...

- *Cabinet „U“ handles GN 425.1 (Aluminum / Stainless Steel, angled)* → Page 107
- *Cabinet „U“ handles GN 427 (Aluminum / Stainless Steel, ellipse shaped profile)* → Page 100
- *Stainless Steel-Cabinet „U“ handles GN 565.5 (ellipse shaped profile)* → Page 82

How to order (Stainless Steel)

1 Material  
2 d<sub>1</sub>  
3 Length l  
4 Finish

GN 425-A4-10-180-GS

How to order (Aluminum)

1 Material  
2 d<sub>1</sub>  
3 Length l  
4 Finish

GN 425-AL-12-125-SW