



1 d_1 Bore B for shaft tol. h11	2 d_2 Bore B for shaft tol. h11	k_1	k_2	d_3 Claming thread	d_4 Claming thread	l_1	l_2	l_3	m	s_1 Square V	s_2 Square V	Clamping kits for d_3	 for d_4
B 8	B 8	16	16	M 4	M 4	52,5	13	13	26,5	-	-	GN 511-M4-16	GN 511-M4-16
B 10	B 8	20	16	M 5	M 4	58	15,5	13	29,5	8	-	GN 511-M5-20	GN 511-M4-16
B 10	B 10	20	20	M 5	M 5	63,5	15,5	15,5	32,5	8	8	GN 511-M5-20	GN 511-M5-20
B 12	B 8	20	16	M 5	M 4	62	16,5	13	32,5	10	-	GN 511-M5-20	GN 511-M4-16
B 12	B 12	20	20	M 5	M 5	71,5	16,5	16,5	38,5	10	10	GN 511-M5-20	GN 511-M5-20
B 15	B 10	25	20	M 6	M 5	75,5	20	15,5	40	12	8	GN 511-M6-25	GN 511-M5-20
B 15	B 12	25	20	M 6	M 5	79,5	20	16,5	43	12	10	GN 511-M6-25	GN 511-M5-20
B 15	B 15	25	25	M 6	M 6	87,5	20	20	47,5	12	12	GN 511-M6-25	GN 511-M6-25
B 16	B 12	25	20	M 6	M 5	81	20	16,5	44,5	-	10	GN 511-M6-25	GN 511-M5-20
B 16	B 16	25	25	M 6	M 6	90,5	20	20	50,5	-	-	GN 511-M6-25	GN 511-M6-25
B 20	B 15	30	25	M 6	M 6	95	22	20	53	16	12	GN 511-M6-30	GN 511-M6-25
B 20	B 16	30	25	M 6	M 6	96,5	22	20	54,5	16	-	GN 511-M6-30	GN 511-M6-25
B 20	B 20	30	30	M 6	M 6	102,5	22	22	58,5	16	16	GN 511-M6-30	GN 511-M6-30

Specification

- Aluminum
 - matt, slide ground
 - anodized, black
- Socket cap screws DIN 912
Stainless Steel AISI 304
- Grub screw DIN 915
Stainless Steel AISI 304
- Stainless Steel characteristics → Page 1489
- RoHS-compliant

Accessory

- Clamping kits GN 511 → Page 1260

Information

Twistable two-way clamp mountings GN 475 connect rods and tubes within the clamp mounting system under any adjustable angle. With the angle adjustment released, the clamp mounting halves stay connected with formlocking effect.

The standard version of the clamping screws at the clamping threads d_3 and d_4 are socket cap screws with hexagonal socket DIN 912. They can be replaced by a clamping kit GN 511 (article code see table of dimensions).

see also...

- Retaining rods / Retaining tubes GN 480.1 → Page 1276
- Twistable two-way clamp mountings GN 490 → Page 1255

How to order	1	d_1
1	2	d_2
2	3	Finish
GN 475-B10-B10-MT		