



3 Type
A Mounting
with countersunk screw

1 r	2 d ₁	b	d ₂	d ₃	l ₁	l ₂	l ₃	l ₄	Load F max. in N
45	M 6	13	19	9	12	13	8,5	0,5	500
65	M 8	18	25	14	14	16	10,5	0,6	1000

Specification

- Latch
 - Zinc die casting
 - plastic coated
 - black, RAL 9005, textured finish
 - silver, RAL 9006, textured finish
 - Indexing mechanism
 - Stainless Steel
 - Countersunk screw DIN 7991
 - Stainless Steel (A2)
 - RoHS compliant
- SW

● SR

Information

Stop locks GN 720 may be used as stops and feature a high degree of stability.

The inside ball-spring latching mechanism has 4 latching positions at a distance of 90° each. Thanks to the bolt attachment using the countersunk screw, the latching position is freely selectable.

The bar is solid and may be machined, if required.

The countersunk screw is enclosed as part of the set.

How to order		1	r
		2	d ₁
		3	Type
		4	Color

1

2

3

4

GN 720-65-M8-A-SW