



ROSTFREI  
Inox  
Stainless  
Steel

2

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub>
16	M 5	16	58	15	5	52,5	9,5
18	M 5	16	72,5	15	5	67	9,5
22	M 6	20	80,5	19,5	6	74	10,5
24	M 6	20	95,5	19,5	6	89	10,5
25	M 6	20	105,5	19,5	6	98,5	10,5

**Specification**

- Handle  
Plastic  
Technopolymer (Polyamide PA)  
- temperature resistant up to 90 °C  
- black, matte finish  
- revolving

KT

- **GN 798.3**  
Retractable mechanism steel  
blackened

- **GN 798.5**  
Retractable mechanism  
Stainless Steel  
- Axle parts AISI 303  
- Flat base  
Sintered Steel AISI 316

• *Stainless Steel characteristics* → Page 1489

• *Plastic characteristics* → Page 1483

• RoHS compliant

**Information**

Typical in design are the retractable handles GN 798.3 / GN 798.5 with their stepped shape consisting of two cylinders giving the operator a better grip, especially when pulling the handle out from its locked position before it can be folded back into the rest position.

Retractable handles GN 798.3 / GN 798.5 are suitable when the handle must be withdrawn during automatic operations.

How to order (Retractable mechanism steel)

1	Material
2	d <sub>1</sub>

**GN 798.3-KT-22**

How to order (Retractable mechanism St. Steel)

1	Material
2	d <sub>1</sub>

**GN 798.5-KT-25**