



3 Type

- A** without bore
- E** with threaded blind bore
- D** with threaded through bore
- C** with plain blind bore H7

1 d ₁	2 d ₂ Thread Type D Type E	2 d ₃ H7 Bore Type C	d ₄	h ₁	h ₂	t ₁ min.	t ₂
40	M 6	-	18	30,5	15	12	13
40	M 8	B 8	18	30,5	15	15	13
50	M 8	-	21	34	17	15	16
50	M 10	B 10	21	34	17	18	16
60	M 10	-	25	39	18	18	20
60	M 12	B 12	25	39	18	22	20

Specification

- **GN 5335**
Stainless Steel AISI 303 (A1)
- matt shot-blasted —
- highly polished **PL**
(only Type D and E)
- **GN 5335.4**
Stainless Steel AISI 316L (A4)
matt shot-blasted —
- *Cross hole GN 110 → Page 317*
- *ISO-Fundamental Tolerances → Page 323*
- *Stainless Steel characteristics → Page 334*
- **RoHS compliant**

Information

Stainless Steel-Star knobs GN 5335 / GN 5335.4 are a special development intended for the food processing machinery industry. The smooth and enclosed areas as well as the large corner radii comply with the requirements of hygiene standards.

see also...

- *Stainless Steel-Star knobs GN 5334 → Page 62/63*
- *Stainless Steel-Wing nuts GN 834 → Main Catalogue Page 306*
- *Stainless Steel-Knurled nuts GN 536 → Main Catalogue Page 321*

How to order (Stainless Steel AISI 303, A1)	1 d ₁
	2 d ₂
1 2 3 4 GN 5335-50-M10-D-PL	3 Type
	4 polished

How to order (Stainless Steel AISI 316L, A4)	1 d ₁
	2 d ₂ (d ₃)
1 2 3 GN 5335.4-40-M8-E	3 Type