



1 d ₁	2 d ₂	3 l ₁ Nominal length						l ₂		d ₃		d ₄	h ₁	h ₂
								MS-pad	KU-pad	MS-pad	KU-pad			
25	M 5	10	15	20	25	-	0,5	1	3	3	3	12	16	8
32	M 6	10	16	20	25	30	1	1,3	4	3,5	3,5	14	20	10
40	M 8	20	25	30	40	50	1,5	1,6	6	5	5	18	25	13
50	M 10	20	25	30	45	55	2	1,9	8	6,5	6,5	22	32	17

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
black, matt finish
- Threaded bolt
Stainless Steel AISI 304 Cu
- Pivot
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- Stainless Steel characteristics → Page 1144
- Plastic characteristics → Page 1141
- RoHS compliant

Information

Star knobs GN 6336.10 with brass or plastic thrust pad are used when indentations or damage is to be avoided.

see also...

- Knurled screws GN 421.10 → Page 319

How to order	1	d ₁
	2	d ₂
	3	l ₁
	4	Material thrust pad

GN6336.10-32-M6-20-KU