



Rost
frei | Inox
Stainless
Steel

4 Form

- A** only with retaining ring
- H** with retaining cable
- K** with ball chain

d₁	d₂	Length l					d₃	h₁	h₂	h₃	r	s	t
25*	M 5	10	15	20	25	25	12	16	8	2,5	19	2,8	-
32	M 6	16	20	25	30	30	14	20	10	3,5	20	3	12
40	M 8	20	25	30	40	40	18	25	13	4	22	3,2	14
50	M 10	20	25	30	45	22	32	17	5	24	3,4	18	
63	M 12	30	40	50	-	26	40	21	5,5	25	3,6	22	

* This size is only available with threaded stud.

Specification

- Sterngriff DIN 6336
Plastic
Thermoplast (Polyamide PA)
black, matt
- Bushing
Stainless Steel AISI 303
- Threaded stud
Stainless Steel
- M5 ... M10: 304 Cu
- M12: AISI 303
- Retaining ring GN 111.6
Stainless Steel AISI 301
- Ball chain GN 111.5 (Type K)
Stainless Steel AISI 301
- Retaining cable GN 111.2 (Type H)
Stainless Steel
coated with clear plastic
- RoHS compliant

On request

- Ball chains / Retaining cables with other lengths
- with spiral retaining cable GN 111.4
- other GN standards with loss protection

Information

Star knobs GN 6336.13 can be captive-attached to a base element with the help of a ball chain or a retaining cable.

The star knobs are supplied ready assembled (with retaining ring and ball chain or retaining cable).

see also...

- *Stainless Steel-Ball chains GN 111.5 → Main Catalogue Page 477*
- *Retaining cables GN 111.2 → Main Catalogue Page 478*
- *Spiral retaining cables GN 111.4 → Main Catalogue Page 479*
- *Retaining rings GN 111.6 → Page 134*

Star knob	1	d ₁
GN 6336.13-40-M8-A	2	d ₂
	3	Type

Star knob with threaded stud	1	d ₁
GN 6336.13-50-M10-30-K	2	d ₂
	3	Length l
	4	Type