



4 Type
C with tapped hole,
no bushing
E with tapped bushing

d ₁	d ₂		KT Type C Thread		d ₃		KT Type E Thread		d ₄ ≈	h ≈	t ₁ min.	t ₂ min.
10	M 3	-	-	-	-	-	-	-	5	9,3	6	-
12	M 4	-	-	-	-	-	-	-	6	11,2	6	-
16	M 4	M 5	-	M 4	M 5	M 4**	-	-	8	15	6	6
20	M 5	M 6	-	M 5	M 6	M 5	-	M 5	12	18	7,5	7,5
25	M 5	M 6	M 8	M 6	M 8	M 6	M 8*	M 6	15	22,5	9	9
30	M 8	-	-	-	-	-	-	-	15	28	12	-
32	M 6	M 8	M 10	M 8	M 10	M 8	-	M 8	18	29	12	12
35	M 10	-	-	-	-	-	-	-	18	32,5	15	-
40	M 8	M 10	M 12	M 10	M 12	M 10	-	-	22	37	15	15
50	M 12	M 14	-	-	-	M 12	-	-	28	46	18	18

* This size is only available in black with bushing in steel. ** This size is only available in black with bushing in brass.

Specification

- 1

 - Plastic
Duroplast (Phenolic PF)
- Flash removed and polished
- black (standard color)
- red **RT**, similar RAL 3003:
add RT on order code
 - Bushing (Type E)
- Steel, zinc plated (standard)
- Brass **MS**
ad MS on order code
- KT

 - Plastic
Technopolymer (Polyamide PA)
- shock resistant
- black, matte finish (standard color)
- red **RT**, similar RAL 3000:
add RT on order code
 - Bushing (Type E)
Steel, zinc plated

• Plastic characteristics → Page 1483

• RoHS compliant

Information

- see also...
- Ball knobs, Press on type DIN 319 → Page 48

How to order	1 Material
1	2 d ₁
2	3 d ₂ (d ₃)
3	4 Type
DIN 319-KU-25-M6-C	