



ROSTSTAHL®
Rostfrei
Inox
Stainless
Steel

3 Type

- A with 2 key rings
- B with tab and key ring
- C with 2 tabs
- D with 2 loops
- E with tab and loop

Length l	d ₁	d ₂	Static load in N ≈		Type A and Type B are suitable for ball lock pins and locking pins with axial lock
			with key ring	without key ring	
150	14 *	1	50	1800	* GN 113.1, GN 113.3, GN 113.4, GN 113.7, GN 113.8, GN 113.9, GN 113.10, GN 214.2, GN 214.3, GN 214.6 for pins Ø 5, Ø 6, Ø 8 and GN 113.5, GN 113.6, GN 114.2, GN 114.3, GN 114.6, GN 124.1, GN 124.2 for all pins
150	18 **	1,3	90	1800	
150	24	1,5	100	1800	
150	30	1,8	120	1800	
200	14 *	1	50	1800	
200	18 **	1,3	90	1800	
200	24	1,5	100	1800	
200	30	1,8	120	1800	
320	14 *	1	50	1800	
320	18 **	1,3	90	1800	
320	24	1,5	100	1800	** GN 113.1, GN 113.3, GN 113.4, GN 113.7, GN 113.8, GN 113.9, GN 113.10, GN 214.2, GN 214.3, GN 214.6 for pins Ø 10, Ø 12, Ø 16, Ø 20, Ø 25
320	30	1,8	120	1800	
500	14 *	1	50	1800	
500	18 **	1,3	90	1800	
500	24	1,5	100	1800	
500	30	1,8	120	1800	