



材質與表面處理

- 固定座：尼龍(PA6+GF)·黑色。
- 手握柄：鋁合金(6063)·包括鋁本色及黑色兩種。

特徵

- 固定座與手握柄兩色區別·外型美觀。
- 安裝迅速·從外向板面固定螺絲·板面可攻牙·或沖孔用螺母固定·而不受內部狹小影響作業。
- 固定座耐酸鹼、耐油、耐熱 -20°C ~ 150°C。
- 材料符合UL94 HB防火等級。
- 附件包：兩根M8*50mm螺絲-合金鋼材質·兩顆螺帽-鐵鍍鋅。

MATERIAL AND FINISH

- Holder: Nylon(PA6+GF), Black.
- Handle: Aluminum alloy (6063), Anodized in natural or black color.

FEATURES

- Could be quick installed on the panel with a tapped hole or with a normal hole by nut.
- Tight the screw from outside, working space is not effected by the cabinet inner space.
- Weathering resistance of PA holder is -20°C~150°C, resistance to acid, alkali, greasiness.
- Use the original raw material compliant with UL94 HB standards.
- With screws pack: Screws M8*50mm 2pcs, and nuts 2pcs.

SPECIFICATION:

Unit:mm

產品編號 Item No.	尺寸 Dimensions			荷重 Load Capacity (kgf)	重量 Weight (g)
	鋁本色 Aluminum Color	黑色 Black Color	P		
E-69180-8	E-69180-9	218	98	100	290
E-69250-8	E-69250-9	288	168		344
E-69300-8	E-69300-9	338	218		377
E-69350-8	E-69350-9	388	268		420
E-69400-8	E-69400-9	438	318		458
E-69500-8	E-69500-9	538	418		531