





26
Possible combinations
of radial insert ball bearings
with cast iron or sheet steel
 housings, corrosion-resistant

Radial insert ball bearing ¹⁾	Cast iron housing ¹⁾ Plummer block housing	
Designation Shaft diameter d	ASE	
GRAE..-XL-NPP-B-FA125 20 mm – 60 mm		PASE..-XL-N-FA125
GE..-XL-KRR-B-FA125 20 mm – 50 mm		RASE..-XL-N-FA125
SUC 12 mm – 30 mm		Available by agreement

Catalogue range; other dimensions and combinations available by agreement.

Further information: SG 1 ► <https://www.schaeffler.de/std/1D60>

Housing selection wizard: ► <https://www.schaeffler.de/std/1D61>

¹⁾ With Corrotect coating.