



Jシリーズは**カタログ記号+J+穴径**にてご注文ください。

*寸法表の背景色はJシリーズの形状図を表しております。

穴径 H7		ご注文数 1~4個のJシリーズ単価 (円)																	
キー溝 Js9		10	12	14	15	16	17	18	19	20	22	25	28	30	32	35	40	45	50
タップ		4 x 1.8			5 x 2.3			6 x 2.8			8 x 3.3			10 x 3.3		12 x 3.3	14 x 3.8		
カタログ記号		-																	
SSA2-15 J 穴径		1,310	2,350																
SSA2-18 J 穴径		1,450	2,490	2,490	2,490														
SSA2-20 J 穴径			1,550	2,590	2,590	2,590	2,590												
SSA2-24 J 穴径			1,760	2,800	2,800	2,800	2,800	2,800	2,800	2,800									
SSA2-25 J 穴径			1,780	2,840	2,840	2,840	2,840	2,840	2,840	2,840	2,840								
SSA2-28 J 穴径					1,980	3,050	3,050	3,050	3,050	3,050	3,050	3,050							
SSA2-30 J 穴径					2,110	3,180	3,180	3,180	3,180	3,180	3,180	3,180	3,180						
SSA2-32 J 穴径					2,150	3,230	3,230	3,230	3,230	3,230	3,230	3,230	3,230	3,230					
SSA2-35 J 穴径					2,400	3,500	3,500	3,500	3,500	3,500	3,500	3,500	3,500	3,500	3,500				
SSA2-36 J 穴径					2,420	3,520	3,520	3,520	3,520	3,520	3,520	3,520	3,520	3,520	3,520				
SSA2-40 J 穴径								2,690	3,830	3,830	3,830	3,830	3,830	3,830	3,830	3,830			
SSA2-45 J 穴径								2,960	4,110	4,110	4,110	4,110	4,110	4,110	4,110	4,110	4,110		
SSA2-48 J 穴径								3,310	4,480	4,480	4,480	4,480	4,480	4,480	4,480	4,480	4,480	4,480	
SSA2-50 J 穴径								3,490	4,650	4,650	4,650	4,650	4,650	4,650	4,650	4,650	4,650	4,650	4,650
SSA2-55 J 穴径								3,890	5,080	5,080	5,080	5,080	5,080	5,080	5,080	5,080	5,080	5,080	5,080
SSA2-56 J 穴径								3,910	5,100	5,100	5,100	5,100	5,100	5,100	5,100	5,100	5,100	5,100	5,100
SSA2-60 J 穴径								4,300	5,490	5,490	5,490	5,490	5,490	5,490	5,490	5,490	5,490	5,490	5,490
SSA2-70 J 穴径								5,510	6,700	6,700	6,700	6,700	6,700	6,700	6,700	6,700	6,700	6,700	6,700
SSA2-80 J 穴径								6,450	7,600	7,600	7,600	7,600	7,600	7,600	7,600	7,600	7,600	7,600	7,600
SSA2-100 J 穴径								9,060	10,250	10,250	10,250	10,250	10,250	10,250	10,250	10,250	10,250	10,250	10,250
SSA2.5-15 J 穴径			1,520	2,690	2,690														
SSA2.5-18 J 穴径			1,640	2,810	2,810	2,810	2,810	2,810	2,810										
SSA2.5-20 J 穴径					1,880	3,050	3,050	3,050	3,050	3,050									
SSA2.5-24 J 穴径					2,170	3,370	3,370	3,370	3,370	3,370	3,370	3,370	3,370						
SSA2.5-25 J 穴径					2,200	3,410	3,410	3,410	3,410	3,410	3,410	3,410	3,410	3,410					
SSA2.5-28 J 穴径								2,520	3,760	3,760	3,760	3,760	3,760	3,760	3,760				
SSA2.5-30 J 穴径								2,670	3,940	3,940	3,940	3,940	3,940	3,940	3,940				
SSA2.5-32 J 穴径								2,830	4,110	4,110	4,110	4,110	4,110	4,110	4,110	4,110			
SSA2.5-35 J 穴径								3,080	4,350	4,350	4,350	4,350	4,350	4,350	4,350	4,350	4,350		
SSA2.5-36 J 穴径								3,220	4,510	4,510	4,510	4,510	4,510	4,510	4,510	4,510	4,510		
SSA2.5-40 J 穴径											3,740	5,110	5,110	5,110	5,110	5,110	5,110	5,110	
SSA2.5-45 J 穴径											4,230	5,620	5,620	5,620	5,620	5,620	5,620	5,620	5,620
SSA2.5-48 J 穴径											4,730	6,080	6,080	6,080	6,080	6,080	6,080	6,080	6,080
SSA2.5-50 J 穴径											5,090	6,460	6,460	6,460	6,460	6,460	6,460	6,460	6,460
SSA2.5-55 J 穴径											5,820	7,200	7,200	7,200	7,200	7,200	7,200	7,200	7,200
SSA2.5-56 J 穴径											5,860	7,240	7,240	7,240	7,240	7,240	7,240	7,240	7,240
SSA2.5-60 J 穴径											6,430	7,770	7,770	7,770	7,770	7,770	7,770		
SSA2.5-70 J 穴径											8,200	9,570	9,570	9,570	9,570	9,570	9,570	9,570	
SSA2.5-80 J 穴径											10,130	11,520	11,520	11,520	11,520	11,520	11,520	11,520	11,520

ご注文数 5~20 個までの単価は巻末の価格表又は Web をご覧ください。

- 【Jシリーズの注意】
- ①受注生産品のため、受注後**実働 2 日以内**（受注日除く）でメーカー完成となります。
 - ②対応数は**1~20 個**です。20 個を超える場合は、別途見積りとさせていただきます。
 - ③キー溝は JIS B 1301 の普通形 (Js9) を採用しています。
 - ④穴、キー加工後の再黒染めをしません。

平歯車

はすば歯車

内歯車

ラック

コラムピニオン

マイタ

かさ歯車

ねじ歯車

ウォームギヤ

ギヤボックス

その他