
60A 20

TYPE 歯数

スプロケットNo.





- ■チェーン ··········No.60
- ■チェーンピッチ ·······(P)19.05mm
- ■ローラリンク内幅 ·······(W)12.70mm
- ■ローラ外径 ·······(Dr) 11.91mm
- ■歯幅·······(T)11.7 mm

m :	普通錦
-----	-----

. 1	TYPE	歯数	外径 Do	ピッチ径 Dp	軸穴 下穴	【径d 最小	重量 kg	¥	Semi-F ¥
		10	70	61.65	14	15	0.27	530	
		11	76	67.62	14	15	0.30	580	
		12	83	73.60	14	15	0.38	560	
-		13	89	79.60	14	15	0.45	640	
		14	95	85.61	16	17	0.50	680	
		15	101	91.62	16	17	0.60	760	
		16	107	97.65	16	17	0.65	820	
		17	113	103.67	16	17	0.75	900	
		18	119	109.71	16	17	0.84	990	
		19	126	115.74	16	17	0.93	1,100	
-		20	132	121.78	16	17	1.05	1,140	シリーズ追加検討中
		21	138	127.82	16	17	1.15	1,220	
		22	144	133.86	16	17	1.25	1,380	
		23	150	139.90	16	17	1.40	1,560	
•	60A	24	156	145.95	18	19	1.50	1,540	ス。
	OUA	25	162	151.99	18	19	1.62	1,630	温
		26	168	158.04	18	19	1.78	1,850	検 討 中
_		27	174	164.09	18	19	1.90	1,920	
		28	180	170.14	18	19	2.05	2,060	
		29	187	176.20	18	19	2.20	2,580	
		30	193	182.25	18	19	2.35	2,300	
-		31	199	188.30	20	21	2.50	2,900	
		32	205	194.35	20	21	2.68	2,540	
		33	211	200.41	20	21	2.85	3,300	
		34	217	206.46	20	21	3.02	3,000	
-		35	223	212.52	20	21	3.25	2,880	
		36	229	218.57	20	21	3.40	3,300	
		37	235	224.63	20	21	3.60	4,050	
_		38	241	230.69	20	21	3.80	3,660	
		39	247	236.74	20	21	4.00	4,380	