



型式表示方法



配管バリエーション



1(P)-ワンタッチ・2(A)-ワンタッチ 1(P)-おねじ・2(A)-ワンタッチ 1(P)-ワンタッチ・2(A)-おねじ 1(P)-おねじ・2(A)-おねじ

		2(A) 適用チューブ外径(mm)				
		φ4	φ6	φ8	φ10	φ12
適用チューブ外径 mm	φ4	●				
	φ6	●	●			
	φ8		●	●		
	φ10			●	●	
	φ12				●	●

		2(A) 適用チューブ外径(mm)				
		φ4	φ6	φ8	φ10	φ12
管接続口径 R	M5	●	●			
	1/8	●	●	●		
	1/4		●	●	●	●
	3/8		●	●	●	●
	1/2				●	●

		2(A) 管接続口径 R				
		M5	1/8	1/4	3/8	1/2
適用チューブ外径 mm	φ4	●	●			
	φ6	●	●	●	●	
	φ8		●	●	●	●
	φ10			●	●	●
	φ12			●	●	●

		2(A) 管接続口径 R				
		M5	1/8	1/4	3/8	1/2
管接続口径 R	M5	●				
	1/8	●	●			
	1/4		●	●		
	3/8			●	●	
	1/2				●	●

VM

VMG

VR

VR51

VHK

VH

VHS□

VHS