

插頭(P)

公螺牙型



本體尺寸	管連接口徑	型式
M5	M5×0.8	KK2P-M5M
	R1/8	-01MS
1/8	R1/8	KK3P-01MS
	R1/4	-02MS
	R3/8	-03MS
	R1/8	KK4P-01MS
1/4	R1/4	-02MS
	R3/8	-03MS
	R1/2	-04MS
	R3/8	KK6P-03MS
1/2	R1/2	-04MS
	R3/4	-06MS

母螺牙型



本體尺寸	管連接口徑	型式
M5	M5×0.8	KK2P-M5F
1/8	Rc1/8	KK3S-01F
	Rc1/4	-02F
	Rc3/8	-03F
1/4	Rc1/4	KK4P-02F
	Rc3/8	-03F
1/2	Rc3/8	KK6P-03F
	Rc1/2	-04F

附螺帽管接頭型(含膠布聚氯酯軟管用)



本體尺寸	適用軟管 內徑(φ)mm	型式
1/8	5/8	KK3P-50N
	6/9	-60N
	6.5/10	-65N
1/4	5/8	KK4P-50N
	6/9	-60N
	6.5/10	-65N
	8/12	-80N
	8.5/12.5	-85N
1/2	8/12	KK6P-80N
	8.5/12.5	-85N
	11/16	-110N

附快速接頭直線型



本體尺寸	適用軟管管外徑mm	型式
M5	3.2	KK2P-23H
	4	-04H
	6	-06H
1/8	4	KK3P-04H
	6	-06H
	8	-08H
	10	-10H
	6	KK4P-06H
1/4	8	-08H
	10	-10H
	12	-12H
1/2	12	KK6P-12H
	16	-16H

附快速接頭L型



本體尺寸	適用軟管管外徑mm	型式
M5	3.2	KK2P-23L
	4	-04L
	6	-06L
1/8	4	KK3P-04L
	6	-06L
	8	-08L
	10	-10L
	6	KK4P-06L
1/4	8	-08L
	10	-10L
	12	-12L
	12	KK6P-12L
1/2	16	-16L

附快速接頭隔板型



本體尺寸	適用軟管管外徑mm	型式
M5	3.2	KK2P-23E
	4	-04E
	6	-06E
1/8	4	KK3P-04E
	6	-06E
	8	-08E
	10	-10E
	6	KK4P-06E
1/4	8	-08E
	10	-10E
	12	-12E
	12	KK6P-12E
1/2	16	-16E

插座(S)

公螺牙型



本體尺寸	管連接口徑	型式
M5	M5×0.8	KK2S-M5M
	R1/8	-01MS
1/8	R1/8	KK3S-01MS
	R1/4	-02MS
	R3/8	-03MS
	R1/8	KK4S-01MS
1/4	R1/4	-02MS
	R3/8	-03MS
	R1/2	-04MS
	R3/8	KK6S-03MS
1/2	R1/2	-04MS
	R3/4	-06MS

母螺牙型



本體尺寸	管連接口徑	型式
M5	M5×0.8	KK2S-M5F
1/8	Rc1/8	KK3S-01F
	Rc1/4	-02F
	Rc3/8	-03F
1/4	Rc1/4	KK4S-02F
	Rc3/8	-03F
1/2	Rc3/8	KK6S-03F
	Rc1/2	-04F

附螺帽管接頭型(含膠布聚氯酯軟管用)



本體尺寸	適用軟管 內徑(φ)mm	型式
1/8	5/8	KK3S-50N
	6/9	-60N
	6.5/10	-65N
1/4	5/8	KK4S-50N
	6/9	-60N
	6.5/10	-65N
	8/12	-80N
	8.5/12.5	-85N
1/2	8/12	KK6S-80N
	8.5/12.5	-85N
	11/16	-110N

附快速接頭直線型



本體尺寸	適用軟管管外徑mm	型式
M5	3.2	KK2S-23H
	4	-04H
	6	-06H
1/8	4	KK3S-04H
	6	-06H
	8	-08H
	10	-10H
	6	KK4S-06H
1/4	8	-08H
	10	-10H
	12	-12H
1/2	12	KK6S-12H
	16	-16H

附快速接頭L型



本體尺寸	適用軟管管外徑mm	型式
M5	3.2	KK2S-23L
	4	-04L
	6	-06L
1/8	4	KK3S-04L
	6	-06L
	8	-08L
	10	-10L
	6	KK4S-06L
1/4	8	-08L
	10	-10L
	12	-12L
	12	KK6S-12L
1/2	16	-16L

附快速接頭隔板型



本體尺寸	適用軟管管外徑mm	型式
M5	3.2	KK2S-23E
	4	-04E
	6	-06E
1/8	4	KK3S-04E
	6	-06E
	8	-08E
	10	-10E
	6	KK4S-06E
1/4	8	-08E
	10	-10E
	12	-12E
	12	KK6S-12E
1/2	16	-16E