FULL EXTENSION SLIDE ESR2031

LOAD CAPACITY 127~167 N/pair | L=R | SUS

- Full extension (3 members).

[Remarks]
- Be sure to read the "Cautions" 1.

[Recommended Screws]
- M3 screw with binding or truss head



No.	Part Name	Material	Finish
①	Outer Member	Stainless Steel (SUS304)	Plain
②	Intermediate Member		
③	Inner Member		
④	Retainer		
⑤	Balls		–

Sold by piece.

RoHS	CAD	Item Code	Item Name	Slide Length	Travel Length	A	B	C	D	Load Capacity N/pair	Load Capacity kgf/pair	Weight (kg/pc)	Box (pcs)	Carton (pcs)
G	3D	190-011-656	ESR2031-200	200	229	–	–	145	160	167	17	0.20	96	–
G	3D	190-011-657	ESR2031-250	250	269			195	210			0.25	48	–
G	3D	190-011-658	ESR2031-300	300	329		160	245	260			0.30	48	–
G	3D	190-011-659	ESR2031-350	350	369		210	295	310			0.35	48	–
G	3D	190-011-660	ESR2031-400	400	429		260	345	360			0.40	48	–
G	3D	190-011-661	ESR2031-450	450	469	205	310	395	410	157	16	0.45	48	–
G	3D	190-011-662	ESR2031-500	500	529	230	360	445	460	127	13	0.50	48	–

Refer to 1 : P.549