


電鍍鑄鐵曲柄把手 HMB 系列
Castiron cranked handles

HMB


series



噴砂曲柄把手 HM-A 系列
Sandblast-plate cranked handles

HM-A

series



尺寸單位 Unit : mm

型號 Model No.		A	圓孔 B/bore	四方孔 C/square	D	E	F	G	手柄型號 Handle is Included	毛重 G.W.
圓孔 B/bore	四方孔 C/square									
HMB-80	HMB-80-SQ	80	10	V10	24	23	22	5/16"	HHPR-23-5/16	0.2kg
HMB-100	HMB-100-SQ	100	10	V12	28	23	28	5/16"	HHPR-23-5/16	0.3kg
HMB-125	HMB-125-SQ	125	10	V14	34	23	34	5/16"	HHPR-23-5/16	0.6kg
HMB-150	HMB-150-SQ	150	14	V17	38	26	38	3/8"	HHPR-26-3/8	0.7kg
HMB-160	HMB-160-SQ	160	14	V17	38	26	38	3/8"	HHPR-26-3/8	0.8kg
HMB-200	HMB-200-SQ	200	17	V22	44	28	44	3/8"	HHPR-28-3/8	1.1kg
HMB-250	HMB-250-SQ	250	17	V22	48	28	48	3/8"	HHPR-28-3/8	1.5kg

型號 Model No.		A	圓孔 B/bore	四方孔 C/square	D	E	F	G	手柄型號 Handle is Included	毛重 G.W.
圓孔 Bore	四方孔 Square									
HM-80A	HM-80A-SQ	80	10	V10	24	19	22	5/16"	HIA-5/16	0.3kg
HM-100A	HM-100A-SQ	100	10	V12	28	19	28	5/16"	HIA-5/16	0.4kg
HM-125A	HM-125A-SQ	125	10	V14	34	19	34	5/16"	HIA-5/16	0.7kg
HM-150A	HM-150A-SQ	150	14	V17	38	24	38	3/8"	HIA-3/8	0.9kg
HM-160A	HM-160A-SQ	160	14	V17	38	24	38	3/8"	HIA-3/8	1 kg
HM-200A	HM-200A-SQ	200	17	V22	44	24	44	3/8"	HIA-3/8	1.4kg
HM-250A	HM-250A-SQ	250	17	V22	48	24	48	3/8"	HIA-3/8	1.7kg

註：以上型號把手附手柄，HM-A系列，若要額外手柄請另外選購第 26~31 頁的產品。
Handle is included HHPR series. Optional handle please refer to page 26-31.