

## Screw plugs with collar and hexagon socket DIN 908

### Item description/product images




#### Description

**Material:**  
Steel.

**Version:**  
Electro zinc-plated.

**Note:**  
Screw plugs with collar and hexagon socket for plugging holes with parallel threads.

### Drawings



### Overview of items

#### Screw plugs with collar and hexagon socket DIN 908

| Order No.    | D  | D1      | K | L  | SW |
|--------------|----|---------|---|----|----|
| K1130.100810 | 12 | M8x1    | 3 | 8  | 4  |
| K1130.101010 | 14 | M10X1   | 3 | 8  | 5  |
| K1130.101215 | 17 | M12X1,5 | 3 | 12 | 6  |
| K1130.101415 | 19 | M14X1,5 | 3 | 12 | 6  |
| K1130.101615 | 21 | M16X1,5 | 3 | 12 | 8  |
| K1130.101815 | 23 | M18X1,5 | 4 | 12 | 8  |
| K1130.102015 | 25 | M20X1,5 | 4 | 14 | 10 |
| K1130.102215 | 27 | M22X1,5 | 4 | 14 | 10 |
| K1130.102415 | 29 | M24X1,5 | 4 | 14 | 12 |
| K1130.102615 | 31 | M26X1,5 | 4 | 16 | 12 |
| K1130.102720 | 32 | M27X2   | 4 | 16 | 12 |
| K1130.103015 | 36 | M30X1,5 | 4 | 16 | 17 |
| K1130.103320 | 39 | M33X2   | 5 | 16 | 17 |
| K1130.103615 | 42 | M36X1,5 | 5 | 16 | 19 |
| K1130.104215 | 49 | M42X1,5 | 5 | 16 | 22 |
| K1130.104220 | 49 | M42X2   | 5 | 16 | 22 |
| K1130.104815 | 55 | M48X1,5 | 5 | 16 | 24 |
| K1130.104820 | 55 | M48X2   | 5 | 16 | 24 |
| K1130.10018  | 14 | G1/8    | 3 | 8  | 5  |
| K1130.10014  | 18 | G1/4    | 3 | 12 | 6  |
| K1130.10038  | 22 | G3/8    | 3 | 12 | 8  |
| K1130.10012  | 26 | G1/2    | 4 | 14 | 10 |
| K1130.10034  | 32 | G3/4    | 4 | 16 | 12 |
| K1130.10100  | 39 | G1      | 5 | 16 | 17 |
| K1130.10114  | 49 | G1 1/4  | 5 | 16 | 22 |
| K1130.10112  | 55 | G1 1/2  | 5 | 16 | 24 |