


LQ1 系列

外形尺寸圖

陽牙接頭：LQ1H-M



(A) 為旋入後的參考尺寸。
 (E) 為從螺帽端面的必要管插入代表編號參考尺寸。
 W為對邊尺寸。

毫米尺寸

型式	適用管 外徑	連接螺牙 R·NPT	A	E	H	L	M	W
LQ1H11-M□	ø4	1/8"	21	10	—	25	11.5	10
LQ1H12-M□	ø3							
LQ1H21-M□	ø6	1/8"	31.5	15	14	35	16.5	14
LQ1H22-M□	ø4							
LQ1H23-M□	ø6	1/4"	29					
LQ1H24-M□	ø4							
LQ1H31-M□	ø10	1/4"	36.5					
LQ1H32-M□	ø8							
LQ1H33-M□	ø6			20	17	42.5	23	19
LQ1H34-M□	ø10							
LQ1H35-M□	ø8	3/8"	36					
LQ1H36-M□	ø6							
LQ1H41-M□	ø12	3/8"	46					
LQ1H42-M□	ø10			24	21	52	28	23
LQ1H43-M□	ø12	1/2"	44					
LQ1H44-M□	ø10							
LQ1H51-M□	ø19	1/2"	55					
LQ1H52-M□	ø12			29	26	62.5	39	32
LQ1H53-M□	ø19	3/4"	53.5					
LQ1H54-M□	ø12							
LQ1H61-M□	ø25	3/4"	72					
LQ1H62-M□	ø19			39.5	36	81	49	46
LQ1H63-M□	ø25	1"	71					
LQ1H64-M□	ø19							

英吋尺寸

型式	適用管 外徑	連接螺牙 Rc·NPT	A	E	H	L	M	W
LQ1H1A-M□	1/8"	1/8"	21	10	—	25	11.5	10
LQ1H2A-M□	1/4"							
LQ1H2B-M□	3/16"	1/8"	31.5	15	14	35	16.5	14
LQ1H2C-M□	1/8"							
LQ1H2D-M□	1/4"	1/4"	29					
LQ1H2E-M□	3/16"							
LQ1H2F-M□	1/8"							
LQ1H3A-M□	3/8"	1/4"	36.5	20	17	42.5	23	19
LQ1H3B-M□	1/4"							
LQ1H3C-M□	3/8"	3/8"	36					
LQ1H3D-M□	1/4"							
LQ1H4A-M□	1/2"	3/8"	46	24	21	52	28	23
LQ1H4B-M□	3/8"							
LQ1H4C-M□	1/2"	1/2"	44					
LQ1H4D-M□	3/8"							
LQ1H5A-M□	3/4"	1/2"	55	29	26	62.5	39	32
LQ1H5B-M□	1/2"							
LQ1H5C-M□	3/4"	3/4"	53.5					
LQ1H5D-M□	1/2"							
LQ1H6A-M□	1"	3/4"	72	39.5	36	81	49	46
LQ1H6B-M□	3/4"							
LQ1H6C-M□	1"	1"	71					
LQ1H6D-M□	3/4"							