


BAR LATCH BLL




- Latch bolt snaps into the strike to prevent accidental release.
- Push tab on strike to release.
- When installed reversely, latch bolt is easily released just by pushing the PUSH part (see "Application Example").
- AS parts set for installing to aluminium frame also available. Content of the parts set is as follows.

[Parts Included]

- Pan head tapping screw (SUS)

[Application Example]



Reverse position

Normal position

Can be used in either normal or reverse position.

When installed reversely, latch bolt is easily released just with a single push.

RoHS	CAD	Item Code	Item Name	L	W	A	C ₁	C ₂	C ₃	H ₁	H ₂	P	d	Weight (g)	Screw	Box (pcs)	Carton (pcs)
✓	3D	140-059-073	BLL-45	48	40	13	32	6.5	-	17	4.5	23±3	3.2	28	3×10	20	400
✓	3D	140-059-074	BLL-60	63	46	16	37	8	-	20	6	34±4	4.2	50	3.5×16	20	400
✓	3D	140-059-075	BLL-80	85	65	20	53	10	-	22.5	7	47±7	5	100	4.5×16	10	200
✓	3D	140-059-076	BLL-100	105	80	25	66	12.5	-	26.5	-	59±7	5.5	182	-	10	100
✓	3D	140-059-183	BLL-120	127	100	28.5	80	6.75	15	8	-	56±10	-	270	5×20	8	80
✓	3D	140-059-184	BLL-150	155	120	30.5	95	7.25	16	-	-	74±14	5.2	350	-	6	60




Parts Set for Installing to Aluminium Frame Please refer to the series introduction page 1 for details about AS series.

[AS Parts Set] Parts set of screws and AS nuts used for installing to aluminium frame




RoHS	CAD	Item Code	Item Name	Aluminium Frame	Parts	Weight (set)
✓	-	140-041-521	AS-BLL-60-30-6	30×30 Groove Width 6 mm	Bar Latch BLL-60 : 1 pc AS Nut AS-6M4 : 4 pcs M4×10 Hexagon Socket Button Head Screw : 4 pcs	61
✓	-	140-041-522	AS-BLL-60-30-8	30×30 Groove Width 8 mm	Bar Latch BLL-60 : 1 pc AS Nut AS-8M4 : 4 pcs M4×10 Hexagon Socket Button Head Screw : 4 pcs	85
✓	-	140-041-523	AS-BLL-60-40-8-30-6	Frame: 40×40 Groove Width 8 mm Door: 30×30 Groove Width 6 mm	Bar Latch BLL-60 : 1 pc AS Nut AS-8M4 : 2 pcs M4×10 Hexagon Socket Button Head Screw : 2 pcs AS Nut AS-6M4 : 2 pcs M4×12 Hexagon Socket Button Head Screw : 2 pcs	66
✓	-	140-041-524	AS-BLL-60-40-10-30-8	Frame: 40×40 Groove Width 10 mm Door: 30×30 Groove Width 8 mm	Bar Latch BLL-60 : 1 pc AS Nut AS-10M4 : 2 pcs M4×10 Hexagon Socket Button Head Screw : 2 pcs AS Nut AS-8M4 : 2 pcs M4×14 Hexagon Socket Button Head Screw : 2 pcs	76
✓	-	140-041-525	AS-BLL-80-40-8	40×40 Groove Width 8 mm	Bar Latch BLL-80 : 1 pc AS Nut AS-8M4 : 4 pcs M4×12 Hexagon Socket Button Head Screw : 4 pcs	119
✓	-	140-041-526	AS-BLL-80-40-10	40×40 Groove Width 10 mm	Bar Latch BLL-80 : 1 pc AS Nut AS-10M5 : 4 pcs M5×14 Hexagon Socket Button Head Screw : 4 pcs	131


[Dimensions]




BLL-45



BLL-60



BLL-60



BLL-80

Refer to 1 : P.20, 2 : P.526