


RECESSED PULL HH-JS Screw Mount




[Parts Included]

- Pan head screw M4×10
- Spring washer 4


[How to Install]



[Cut Out Dimensions]



Designed to install by pinching the mounting panel with supplied spacers, spring washers and screws.



No.	Part Name	Material	Finish / Colour
①	Body	ABS + PC	Black, Ivory
②	Spacer	Steel	Clear Zinc Chromate (Trivalent)


RoHS	CAD	Item Code	Item Name	Colour	W1	W2	H1	H2	H3	D1	D2	D3	P	W3	H4	Door Thickness	Weight (g)	Box (pcs)	Carton (pcs)
6	3D	100-024-573	HH-JS70-BL	Black	70	43	38	17	19	10.5		9	58	48	25	0.5~3.2	20	10	200
6	3D	100-024-574	HH-JS70-IV	Ivory													20	10	200
6	3D	100-024-575	HH-JS90-BL	Black	90	63	44	21.5	22	11	3		78	68	31		25	10	200
6	3D	100-024-576	HH-JS90-IV	Ivory													25	10	200
6	3D	100-024-577	HH-JS110-BL	Black	110	82	50	24.4	26	11.5	3.5		96	90	36		38	10	200
6	3D	100-024-578	HH-JS110-IV	Ivory													34	10	200
6	3D	100-024-579	HH-JS140-BL	Black	140	109	64	34	33				126	116	48		56	10	200
6	3D	100-024-580	HH-JS140-IV	Ivory													56	10	200

RECESSED PULL HH-JW Quick Installation





- Easy installation by snap-in.

[How to Install]



One-touch installation.

[Cut Out Dimensions]



[Hole Dimensions]

Item Name	W3	H3			
		Board Thickness 0.8	Board Thickness 1.0-1.2	Board Thickness 1.5-2.0	Board Thickness 2.3
HH-JW70	46	28.7	29	29.4	30.8
HH-JW90	66	34.7	35	35.4	36.8
HH-JW110	88	40.7	41	41.4	42.8
HH-JW140	114	54.7	55	55.4	56.8

RoHS	CAD	Item Code	Item Name	Material	Colour	W1	W2	H1	H2	D1	D2	Weight (g)	Box (pcs)	Carton (pcs)
6	3D	100-024-581	HH-JW70-BL	ABS + PC	Black	70	43	38	18.5	10.5	3	14	10	200
6	3D	100-024-582	HH-JW70-IV		Ivory							14	10	200
6	3D	100-024-583	HH-JW90-BL		Black	90	63	44	22.9	11	3	21	10	200
6	3D	100-024-584	HH-JW90-IV		Ivory							21	10	200
6	3D	100-024-585	HH-JW110-BL		Black	110	83	50	26.8	11.5	3.5	35	10	200
6	3D	100-024-586	HH-JW110-IV		Ivory							35	10	200
6	3D	100-024-587	HH-JW140-BL		Black	140	109	64	37.8			53	10	200
6	3D	100-024-588	HH-JW140-IV		Ivory							54	10	200