

RL = Roller length
EL = Fitting length
AL = Axle length

External cylinder Ø	Roller length	Fitting length	Axle length	Axle type	
mm	mm	mm	mm		kg

Blank steel cylinder conveyor rollers

Sheet steel bearing liner, galvanised with grooved ball bearing



50x1,5	200	210	230	F10	150	S55-F10-210-230
50x1,5	300	310	330	F10	130	S55-F10-310-330
50x1,5	400	410	430	F10	80	S55-F10-410-430
50x1,5	500	510	530	F10	70	S55-F10-510-530
50x1,5	600	610	630	F10	40	S55-F10-610-630
50x1,5	200	220	250	A10	240	S55-A10-220-250
50x1,5	300	320	350	A10	240	S55-A10-320-350
50x1,5	400	420	450	A10	240	S55-A10-420-450
50x1,5	500	520	550	A10	200	S55-A10-520-550
50x1,5	600	620	650	A10	130	S55-A10-620-650
60x1,5	200	222	252	A12	240	S60-A12-222-252
60x1,5	300	322	352	A12	240	S60-A12-322-352
60x1,5	400	422	452	A12	240	S60-A12-422-452
60x1,5	500	522	552	A12	240	S60-A12-522-552
60x1,5	600	622	652	A12	240	S60-A12-622-652
80x2	200	222	252	A12	240	S80-A12-222-252
80x2	300	322	352	A12	240	S80-A12-322-352
80x2	400	422	452	A12	240	S80-A12-422-452
80x2	500	522	552	A12	240	S80-A12-522-552
80x2	600	622	652	A12	240	S80-A12-622-652

Galvanised steel tube support rollers

Conveyor roller bearings made of galvanised sheet steel with deep groove ball bearings

50x1,5	200	210	230	F10	150	S56-F10-210-230
50x1,5	300	310	330	F10	130	S56-F10-310-330
50x1,5	400	410	430	F10	80	S56-F10-410-430
50x1,5	200	220	250	A10	240	S56-A10-220-250
50x1,5	300	320	350	A10	240	S56-A10-320-350
50x1,5	400	420	450	A10	240	S56-A10-420-450
50x1,5	500	520	550	A10	200	S56-A10-520-550
60x1,5	300	322	352	A12	240	S61-A12-322-352
60x1,5	400	422	452	A12	240	S61-A12-422-452
60x1,5	500	522	552	A12	240	S61-A12-522-552
60x1,5	600	622	652	A12	240	S61-A12-622-652

NEW



Axle variants



mm



External thread

10	A10
12	A12



Spring axle

10	F10
----	-----