

Heavy duty apparatus castors

Description

Fork of sheet steel
zinc-chromated
dual-row ball bearings collar in fork head

Model

- Swivel castor
- Swivel castor with total brake



 40 - 100 kg

Tread

Grey rubber

Wheel body

Plastic

Bearing

Ball bearing (80, 150, 200 mm Ø with metal threadguards)



Tread

Grey rubber

Wheel body

Plastic

Bearing

Plain bearing



Tread

Grey rubber, antistatic

Wheel body

Plastic
(200 mm Ø Steel rim)

Bearing

Ball bearing



Lauffläche

Rubber wheel grey, puncture-free

Wheel body

Plastic

Bearing

Ball bearing



Tread

Pneumatic tyre, grey rubber

Wheel body

Plastic

Bearing

Ball bearing



							
mm	mm	kg	mm	mm	mm		

80	21	80	112	12,2	27		C101.A85.081	C121.A85.081
100	30	80	134	12,2	42		C101.A85.100	C121.A85.100
125	31	100	158	12,2	44		C101.A85.125	C121.A85.125
150	32	100	188	12,2	45		C101.A85.151	C121.A85.151
200	32	100	241	12,2	61		C101.A85.200	C121.A85.200

60	20	40	88	12,2	28		C201.A80.060	C221.A80.060
80	21	80	112	12,2	27		C101.A80.081	C121.A80.081
100	30	80	134	12,2	42		C101.A80.100	C121.A80.100
125	31	100	158	12,2	44		C101.A80.125	C121.A80.125
150	32	100	188	12,2	45		C101.A80.151	C121.A80.151

80	30	80	112	12,2	27		C101.A89.080	C121.A89.080
100	32	80	134	12,2	42		C101.A89.100	C121.A89.100
125	32	100	158	12,2	44		C101.A89.125	C121.A89.125
150	32	100	188	12,2	45		C101.A89.150	C121.A89.150
200	32	100	241	12,2	61		C101.A89.200	C121.A89.200

125	32	80	158	12,2	35		C101.A86.125	C121.A86.125
150	35	50	182	12,2	45		C101.A86.150	C121.A86.150

150	30	60	188	12,2	45		C101.D20.150	C121.D20.150
-----	----	----	-----	------	----	--	--------------	--------------