



Description

Sheet steel fork
zinc-chromatised
dual-row ball bearings collar in fork head

Model

- Swivel castor
- Swivel castor with total brake



mm	mm	kg	mm	mm	mm				
50	20	50	73	10,2	26			A301.A85.050	A321.A85.050
75	25	60	103	10,2	38			A301.A85.075	A321.A85.075
100	24	70	121	10,2	39			A301.A85.100	A321.A85.100

50 - 70 kg

50	20	50	73	10,2	26			A301.A80.050	A321.A80.050
75	25	60	103	10,2	38			A301.A80.075	A321.A80.075
100	24	70	121	10,2	39			A301.A80.100	A321.A80.100



Tread
Grey rubber

Wheel body
Plastic

Bearing
Ball bearing



Tread
Grey rubber

Wheel body
Plastic

Bearing
Plain bearing

50	18	50	73	10,2	26			A301.A89.050	A321.A89.050
75	24	60	103	10,2	38			A301.A89.075	A321.A89.075
100	28	70	121	10,2	39			A301.A89.100	A321.A89.100



Tread
Grey rubber, antistatic

Wheel body
Plastic

Bearing
Ball bearing

50	18	50	73	10,2	26			A301.A90.050	A321.A90.050
75	23	50	103	10,2	38			A301.A90.075	A321.A90.075
100	23	65	121	10,2	39			A301.A90.100	A321.A90.100



Tread
Plastic black

Wheel body
Plastic

Bearing
Plain bearing