

## No. 7600S


### Ball pressure screw

Tempered steel, burnished.



NEW!  
NEW!  
NEW!

| Order no. | Size = clamping force [kN] | M1  | L  | SW | Weight [g] |
|-----------|----------------------------|-----|----|----|------------|
| 553353    | 30                         | M16 | 62 | 8  | 80         |
| 554214    | 32                         | M16 | 55 | 8  | 70         |
| 554215    | 40                         | M20 | 65 | 10 | 128        |
| 553441    | 43                         | M20 | 78 | 10 | 165        |
| 554216    | 49                         | M24 | 93 | 12 | 275        |



## No. 7600D

### Pressure pad

Complete with dowel pin.  
Stainless steel.




DG

DR

NEW!  
NEW!

| Order no. | Size = clamping force [kN] | Form | A    | B  | C  | Weight [g] |
|-----------|----------------------------|------|------|----|----|------------|
| 553351    | 30                         | DG   | 19,5 | 25 | 18 | 28         |
| 553352    | 30                         | DR   | 19,5 | 25 | 18 | 27         |
| 553442    | 43                         | DG   | 24,0 | 30 | 20 | 47         |
| 553443    | 43                         | DR   | 24,0 | 30 | 20 | 48         |
| 554301    | 49                         | DG   | 28   | 36 | 25 | 75         |
| 554302    | 49                         | DR   | 28   | 36 | 25 | 78         |



### Recommendations



ISO 2936C



No. 6339, page 95

## No. 7600BF


### Mounting kit

Comprising cylinder screw DIN 6912, strength grade 12.9 and T-groove key DIN 508.



NEW!  
NEW!  
NEW!

| Order no. | Size = clamping force [kN] | A  | M   | L  | SW | Weight [g] |
|-----------|----------------------------|----|-----|----|----|------------|
| 553335    | 30 / 32                    | 14 | M12 | 25 | 10 | 67         |
| 553338    | 30 / 32                    | 16 | M12 | 30 | 10 | 86         |
| 553339    | 30 / 32                    | 18 | M12 | 30 | 10 | 118        |
| 553340    | 30                         | 18 | M16 | 30 | 14 | 141        |
| 553342    | 30                         | 20 | M16 | 35 | 14 | 188        |
| 553343    | 30 / 43                    | 22 | M16 | 40 | 14 | 262        |
| 553344    | 30                         | 24 | M16 | 40 | 14 | 346        |
| 553446    | 40 / 43                    | 18 | M16 | 35 | 14 | 148        |
| 553447    | 40 / 43                    | 20 | M16 | 40 | 14 | 196        |
| 553448    | 40 / 43                    | 24 | M16 | 45 | 14 | 354        |
| 554298    | 49                         | 22 | M20 | 40 | 17 | 298        |
| 554299    | 49                         | 24 | M20 | 45 | 17 | 394        |
| 554300    | 49                         | 28 | M20 | 45 | 17 | 505        |



Subject to technical alterations.