




4 Type (Base plate)

- A1** Steel, zinc plated
rubber inlaid, black
- A2** Steel, zinc plated
rubber inlaid, white

1	2	3										3			
d ₁	d ₂	l ₁										l ₇	h ₁	h ₂	s
		Version S / SK					Version U / UK					Version X			
50	M 8	40	50	63	-	-	-	-	-	-	37	14,5	3,5	3	
50	M 10	50	60	80	100	-	-	-	-	-	40	14,5	3,5	3	
50	M 12	60	80	100	125	-	-	-	-	-	43	14,5	3,5	3	
50	M 16	-	-	-	-	75	100	125	150	200	49	14,5	3,5	3	
60	M 8	40	50	63	-	-	-	-	-	-	38	16	4	3	
60	M 10	50	60	80	100	-	-	-	-	-	41	16	4	3	
60	M 12	60	80	100	125	-	-	-	-	-	45	16	4	3	
60	M 16	-	-	-	-	75	100	125	150	200	50	16	4	3	
80	M 8	40	50	63	-	-	-	-	-	-	40	18	5	3	
80	M 10	50	60	80	100	-	-	-	-	-	43	18	5	3	
80	M 12	60	80	100	125	-	-	-	-	-	47	18	5	3	
80	M 16	-	-	-	-	75	100	125	150	200	52	18	5	3	
80	M 20	-	-	-	-	75	100	125	150	200	60	18	5	3	
80	M 24	-	-	-	-	100	125	150	200	-	-	18	5	3	
100	M 8	40	50	63	-	-	-	-	-	-	42	20	6	3	
100	M 10	50	60	80	100	-	-	-	-	-	45	20	6	3	
100	M 12	60	80	100	125	-	-	-	-	-	49	20	6	3	
100	M 16	-	-	-	-	75	100	125	150	200	54	20	6	3	
100	M 20	-	-	-	-	75	100	125	150	200	62	20	6	3	
100	M 24	-	-	-	-	100	125	150	200	-	-	20	6	3	
120	M 20	-	-	-	-	100	125	150	200	-	65	22	6	4	
120	M 24	-	-	-	-	100	125	150	200	-	-	22	6	4	
120	M 30	-	-	-	-	100	125	150	200	-	-	22	6	4	

Specification

- Base plate, sheet metal
Steel, zinc plated, blue passivated
- Threaded stem
Steel, zinc plated, blue passivated
- Hexagon nut ISO 4032
Steel, zinc plated, blue passivated

- Rubber underlay, inlaid
 - black: Perbunan® (NBR)
80±5 Shore A
 - white: Santoprene® (TPE)
80±5 Shore A

- Elastomer characteristics → Page 1483
- Load rating information → Page 1471
- RoHS compliant