



4 Type (Base plate)

A1 Steel, zinc plated
Rubber, inlaid, black

1		2		3		3												
d ₁	d ₂	l ₁		Version S / SK						Version U / UK				l ₇	h ₁	d ₄	l ₈	l ₉
50	M 8	40	50	63	-	-	-	-	-	-	-	40	18	13	25	45		
50	M 10	50	60	80	100	-	-	-	-	-	-	43	18	13	25	45		
50	M 12	60	80	100	125	-	-	-	-	-	-	47	18	13	25	45		
50	M 16	-	-	-	-	75	100	125	150	200	52	18	13	25	45			
60	M 8	40	50	63	-	-	-	-	-	-	-	41	19	13	25	50		
60	M 10	50	60	80	100	-	-	-	-	-	-	44	19	13	25	50		
60	M 12	60	80	100	125	-	-	-	-	-	-	48	19	13	25	50		
60	M 16	-	-	-	-	75	100	125	150	200	53	19	13	25	50			
80	M 8	40	50	63	-	-	-	-	-	-	-	42	20	13	30	70		
80	M 10	50	60	80	100	-	-	-	-	-	-	45	20	13	30	70		
80	M 12	60	80	100	125	-	-	-	-	-	-	49	20	13	30	70		
80	M 16	-	-	-	-	75	100	125	150	200	54	20	13	30	70			
80	M 20	-	-	-	-	75	100	125	150	200	62	20	13	30	70			
80	M 24	-	-	-	-	100	125	150	200	-	-	20	13	30	70			
100	M 8	40	50	63	-	-	-	-	-	-	-	43	21	13	30	80		
100	M 10	50	60	80	100	-	-	-	-	-	-	46	21	13	30	80		
100	M 12	60	80	100	125	-	-	-	-	-	-	50	21	13	30	80		
100	M 16	-	-	-	-	75	100	125	150	200	55	21	13	30	80			
100	M 20	-	-	-	-	75	100	125	150	200	63	21	13	30	80			
100	M 24	-	-	-	-	100	125	150	200	-	-	21	13	30	80			

Specification

- Base plate / lug, sheet metal
Steel, zinc plated, blue passivated
- Threaded stem
Steel, zinc plated, blue passivated
- Hexagon nut ISO 4032
Steel, zinc plated, blue passivated
- Rubber underlay, inlaid
black, Perbunan® (NBR)
80±5 Shore A
- Elastomer characteristics → Page 330
- Load rating information → Page 231
- RoHS compliant