




4 Type (Base plate)

- B1** matt shot-blasted, rubber inlaid, black
B2 matt shot-blasted, rubber inlaid, white
B3* matt shot-blasted, rubber vulcanised, black
B4* matt shot-blasted, rubber vulcanised, white
C3* polished, rubber vulcanised, black
C4* polished, rubber vulcanised, white

1		2		3		3					3					3					3			
d ₁	d ₂	I ₁ Version S / SK					Version T / TK and U / UK					I ₂ Version V / VK				I ₃ ^{+4.0} ₀ Version W				I ₇ ^{+4.0} ₀ Vers. X		t	A/F ₇	
50	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	37	8	14			
50	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	40	10	14			
50	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	43	12	17			
50	M 16	-	-	-	-	-	75	100	125	150	200	-	-	-	-	-	-	-	49	16	22			
60	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	38	8	14			
60	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	41	10	14			
60	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	45	12	17			
60	M 16	-	-	-	-	-	75	100	125	150	200	75	100	125	150	123	148	173	198	50	16	22		
80	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	8	14			
80	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	43	10	14			
80	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	47	12	17			
80	M 16	-	-	-	-	-	75	100	125	150	200	75	100	125	150	125	150	175	200	52	16	22		
80	M 20	-	-	-	-	-	75	100	125	150	200	100	125	150	200	149	174	199	249	60	20	27		
80	M 24	-	-	-	-	-	100	125	150	200	-	100	150	200	-	174	224	274	-	-	-	-		
100	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	42	8	14			
100	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	45	10	14			
100	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	49	12	17			
100	M 16	-	-	-	-	-	75	100	125	150	200	75	100	125	150	126	151	176	201	54	16	22		
100	M 20	-	-	-	-	-	75	100	125	150	200	100	125	150	200	151	176	201	251	62	20	27		
100	M 24	-	-	-	-	-	100	125	150	200	-	100	150	200	-	176	226	276	-	-	-	-		
120	M 20	-	-	-	-	-	100	125	150	200	-	-	-	-	-	-	-	-	-	65	20	27		
120	M 24	-	-	-	-	-	100	125	150	200	-	-	-	-	-	-	-	-	-	-	-	-		
120	M 30	-	-	-	-	-	100	125	150	200	-	-	-	-	-	-	-	-	-	-	-	-		

* only available for the dimensions d₁ = 60, 80 and 100.

Specification

- Base plate, sheet metal
Stainless Steel AISI 304
- Threaded stem
Stainless Steel AISI 303
- Hexagon nut ISO 4032
Stainless Steel AISI 304
- Rubber underlay, inlaid
 - black: Perbunan® (NBR)
80±5 Shore A
 - white: Santoprene® (TPE)
80±5 Shore A
- Rubber underlay, vulcanised
 - 80±5 Shore A
 - black: Perbunan® (NBR)
 - white: Perbunan® (NBR)
- RoHS compliant