





edelstahl®
Rost
frei
Inox
Stainless
Steel

4 Type (Base plate)

B1 matt shot-blasted,
rubber inlaid, black

1		2		3		3										3					3					
d ₁	d ₂	I ₁ Version S / SK						Version T / TK und U / UK				I ₂ Version V / VK				I ₃ Version W					I ₇ Vers. X	A/F ₇	t			
50	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	14	8			
50	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	43	14	10			
50	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	47	17	12			
50	M 16	-	-	-	-	75	100	125	150	200	-	-	-	-	-	-	-	-	-	-	52	22	16			
60	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	41	14	8			
60	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	44	14	10			
60	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	48	17	12			
60	M 16	-	-	-	-	75	100	125	150	200	75	100	125	150	126	151	176	201	53	22	16					
80	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	42	14	8			
80	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	45	14	10			
80	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	49	17	12			
80	M 16	-	-	-	-	75	100	125	150	200	75	100	125	150	127	152	177	202	54	22	16					
80	M 20	-	-	-	-	75	100	125	150	200	100	125	150	200	151	176	201	251	62	27	20					
80	M 24	-	-	-	-	100	125	150	200	-	100	150	200	-	176	226	276	-	-	-	-	-	-			
100	M 8	40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	43	14	8			
100	M 10	50	60	80	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	46	14	10			
100	M 12	60	80	100	125	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	50	17	12			
100	M 16	-	-	-	-	75	100	125	150	200	75	100	125	150	128	153	178	203	55	22	16					
100	M 20	-	-	-	-	75	100	125	150	200	100	125	150	200	152	177	202	252	63	27	20					
100	M 24	-	-	-	-	100	125	150	200	-	100	150	200	-	177	227	277	-	-	-	-	-	-			

Specification

- Base plate / lug, sheet metal
Stainless Steel AISI 304
- Threaded stem
Stainless Steel AISI 303
- Hexagon nut ISO 4032
Stainless Steel, AISI 304
- Rubber underlay, inlaid
black, Perbunan® (NBR)
80±5 Shore A
- Stainless Steel characteristics
→ Page 1489
- Elastomer characteristics
→ Page 1483
- RoHS compliant