



- 3 Type**
- A** with two-hole flange (d₁ = 60 / 90 / 113)
 - B** with four-hole flange (d₁ = 113 / 126)
- 4 Identification no.**
- 1** without tear-off lock
 - 2** with tear-off lock

1	2	d₁	d₂	d₃	d₄ Type A	d₅ Type B	h	s	b Type A	l₁ Type A	l₂ Type B	m₁ Type A	m₂ Type B
		60	M 10	78	9	-	30	2	78	128	-	110	-
		90	M 12	106	13	-	39	3	110	170	-	140	-
		113	M 16	150	12,5	12,5	52	4	150	216	168	184	132
		126	M 20	177	-	13	63	4	-	-	184	-	150

* not available from stock, requires a minimum order quantity

Specification

- Vibration damping element
Natural rubber (NR)
 - vulcanized
 - temperature resistant up to 80 °C
 - Hardness Shore A ±5
 - soft* **43**
 - medium **57**
 - hard* **68**
- Sheet metal
 - zinc plated, blue passivated
- Threaded insert
 - Steel
 - zinc plated, blue passivated
- Elastomer characteristics → Page 1483
- RoHS compliant

Accessory

- Rubber pads GN 148.2 → Page 1055

Information

Levelling feet GN 148 are designed for setting up heavy machinery and units with insulation against vibrations.

This has a positive impact on the lifetime of machines and additionally reduces the noise pollution.

The structure is such that horizontal forces are also absorbed.

The design with tear-off lock (identification no. 2) protects the levelling feet from destruction caused by tear-off under excessive tension loads.

The details relating to the load bearing capacity are non-binding recommended values and rule out any liability. They constitute no general warranty of quality and condition. The user must determine from case to case whether a product is suitable for the intended use.

see also...

- Determining the suitable levelling foot → Page 1054

How to order	1	d₁
	2	d₂
	3	Type
	4	Identification no.
	5	Hardness

GN 148-113-M16-A-1-57