


- 1 Type**
- Operation with
- SC** key (same lock)
 - SU** key (different lock)
 - SCK** wing knob (same lock)
 - SUK** wing knob (different lock)
 - SCT** T-Handle (same lock)
 - SUT** T-Handle (different lock)

- 3 Version of the hook**
- H1** Pivot radius R=28

- 5 Identification no.**
- 1** without latch bracket
 - 2** with latch bracket



Hook distance A	d		h	
	Type SC, SU	Type SCK, SUK, SCT, SUT	Type SC, SU	Type SCK, SUK, SCT, SUT
18	28	32	4	6

1) Dimensions of the latch bracket → Page 931

Specification

- Lock housing
Zinc die casting
- Locating ring
 - chrome plated **CR**
 - plastic coated **SW**
black, RAL 9005, textured finish
- All other parts
Steel zinc plated, blue passivated
- Key
Nickel silver with plastic hand piece
- Wing knob / T-handle
Plastic (Polyamide PA)
black, matte
- Plastic characteristics → Page 1483
- RoHS compliant

On request

- Hook-type latches
with other hook distance A
- Hook with other pivoting radius R

Information

Hook-type latches GN 115.8 with hook and latch bracket are mainly used for sliding doors and flaps. The locking action is in radial direction to the axis of rotation, resulting in a wide variety of different uses.

Two keys are supplied with the unit. The key can be removed in both end positions.

Hook-type latches GN 115.8 are supplied with loosely enclosed latch.

see also...

- Construction and assembly instructions → Page 931
- List of latch types → Page 892 ff.
- Hook-type latches GN 115.8 (operating with operating elements)
→ Page 930

How to order		1	Type
		2	Latch distance A
		3	Version of the hook
		4	Finish locating ring
		5	Identification no.

GN 115.8-SC-18-H1-SW-1