



Inch sizes available

1 2 3

1		2		3														
l_1	d_1	l_2		d_3	d_4	h_1	h_2	h_3	h_4	Stroke								
30	M 3	-	6	8	10	12	16	-	-	-	10	13	24,5	4	31	3,5		
30	M 4	-	12	16	20	25	32	-	-	-	10	13	24,5	4	31	3,5		
30	M 5	M 6	12	16	20	25	32	40	50	-	10	13	24,5	4	31	3,5		
45	M 4	-	12	16	20	25	32	-	-	-	10	13	24,5	4	34	3,5		
45	M 5	M 6	12	16	20	25	32	40	50	-	10	13	24,5	4	34	3,5		
63	M 6	M 8	12	16	20	25	32	40	50	63	13,5	17,5	31	6,5	45	4		
63	M 10	-	20	25	32	40	50	63	80	-	13,5	17,5	31	6,5	45	4		
78	M 8	M 10	16	20	25	32	40	50	63	80	16	21	36	8	54	4		
78	M 12	-	25	32	40	50	63	80	-	-	16	21	36	8	54	4		
92	M 10	M 12	16	20	25	32	40	50	63	80	19	24	43	11	64	4		
92	M 16	-	25	32	40	50	63	80	-	-	19	24	43	11	64	4		
108	M 12	M 16	25	32	40	50	63	80	120	-	23	30	50,5	12	75	5		

Specification

- Handle
Zinc die casting
- plastic coated
black, RAL 9005, textured finish
black, RAL 9011, silk finish
orange, RAL 2004, textured finish
red, RAL 3000, textured finish
silver, RAL 9006, textured finish
- chrome-plated
- uncoated
slide grinded
- Threaded stud and retaining screw
Steel
- Tensile strength class 5
- blackened
- RoHS compliant

- SW
- SZ
- OS
- RS
- SR
- CR
- RH

Information

Adjustable hand levers GN 300 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Adjustable hand levers GN 300.1 (threaded stud Stainless Steel) → Page 323
- Adjustable Stainless Steel-Hand levers GN 300.5 (matt shot-blasted) → Page 325
- Flat adjustable hand levers GN 302 → Page 335
- Adjustable hand levers GN 300.4 (with increased clamping force) → Page 333
- Adjustable hand levers GN 303 (with push button) → Page 329

How to order

GN 300-63-M8-25-SW

1	l_1
2	d_1
3	l_2
4	Color (Finish)