



- 3 Type**
- A** Mounting from the back (threaded blind bore)
 - B** Mounting from the operator's side (only for $d_1 = 28$)

<div>1</div> <div>d₁</div>	<div>2</div> <div>Length l ±0,25</div>							d ₂	d ₃	b ₁	b ₂	h ₁	h ₂	t min.
20	180	200	250	300	350	400	-	M 6	-	24	12	42	54	12
28	200	250	300	350	400	500	600	M 8	M 6	25	14	50	66	15
30	200	300	350	400	500	600	1000	M 8	-	27	17	51	68	15

Specification

- Handle tube
Aluminum (wall thickness 1,5)
- Handle legs
Zinc die casting
- Tube plastic coated black, RAL 9005, textured finish
Handle legs plastic coated black, RAL 9005, textured finish
- Tube anodized, natural color
Handle legs plastic coated black, RAL 9005, textured finish
- Tube anodized, natural color
Handle legs plastic coated silver, RAL 9006, textured finish
- Cover caps
Plastic, light grey
- Socket button head screws
ISO 7380-M6-20
Steel, black zinc plated
- Hexagon nuts ISO 4032-M6
Steel, zinc plated
- Washers DIN 125
Steel, zinc plated
- Load rating information → Page 1450
- RoHS compliant

Information

The handle tube of the GN 333.1 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles Ø 28 (type A) are available under GN 333.9 → Page 135.

For type B, socket button head screws, hexagon nuts and washers are included.

see also...

- Tubular handles GN 333 (angled) → Page 136
- Stainless Steel-Tubular handles GN 333.5 → Page 134
- Tubular handles GN 331 (with power switching function) → Page 132
- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order	1 d ₁
	2 Length l
	3 Type
	4 Finish