



3 Type

- F with fixed handle
- D with revolving handle

Length l	1 s H11		e min. (Column 1)	2 d ₁ H7		d ₂	h ₁	h ₂	h ₃ ≈	h ₄ ≈		Ø Handle
	1	2		1	2					Type D	Type F	
63	V 10	-	13,1	B 6	20	20	11	32	54,5	50	16	
80	V 10	V 12	13,1	B 8	24	24	13	38	61	56	18	
100	V 12	V 14	16,1	B 10	28	28	13	48	67	64	20	
125	V 14	V 17	18,1	B 10	34	34	14	55	76	72	22	
160	V 17	V 19	22,2	B 14	38	38	14	65	83	80	25	
200	V 19	V 22	25,2	B 17	44	44	21	78	96,5	90	28	
250	V 22	V 24	28,2	B 17	48	48	21	90	105,5	100	32	
315	V 24	V 27	32,2	B 20	54	54	26	105	117	112	36	

Specification

- Body
Cast iron (GGG)
- plastic coated
 black, textured finish
- hub machined
- Fixed handles DIN 39
Steel zinc plated, blue passivated
- Revolving handles DIN 98
Steel zinc plated, blue passivated
- Square DIN 79 → Page 1424
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- RoHS compliant

Information

The hub bores d₁ H7 are not provided for in the official standard sheet.

How to order

DIN 468-100-V14-F

- 1 Length l
- 2 s (d₁)
- 3 Type