



**4 Type**

- A** with handle locking in the folded up or folded down position
- B** with spring return of the handle in the folded down position

**1**

l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>	m <sub>1</sub>	m <sub>2</sub>
100	150	65	121	122	60	134	49
120	170	65	141	142	60	154	49

**Specification**

- Folding handle
  - Steel ● CR
  - chrome-plated
  - Stainless Steel AISI 304 ● NI
  - matt, shot-blasted
- Tray
  - Zinc die casting
  - plastic coated
  - black, RAL 9005, textured finish ● SW
  - silver, RAL 9006, textured finish ● SR
- *Stainless Steel characteristics* → Page 1489
- *Load rating information* → Page 1454
- *RoHS compliant*

**2 3**

**Information**

The folding handles with recessed tray GN 425.8 are used if the handle is to protrude by a maximum of 3 mm when folded down.

In type A, the folding handle is held in both end positions by spring-loaded thrust pieces.

In type B, the folding handle always spring-returns to the starting position after being released, preventing it from protruding with potentially interfering effect.

see also...

- *Folding handles with recessed tray GN 825.2 (Plastic, with spring-loaded return)* → Page 126
- *Folding handles GN 825.1 (Plastic, with spring-loaded return)* → Page 128

**How to order**

<b>1</b>	l <sub>1</sub>
<b>2</b>	Material / Finish handle
<b>3</b>	Finish tray
<b>4</b>	Type

**GN 425.8-120-CR-SW-A**