




| 1        |                             |                          |      | 2              |                | 2           |           |
|----------|-----------------------------|--------------------------|------|----------------|----------------|-------------|-----------|
| Length l | d <sub>1</sub> H7<br>Bore B | d <sub>2</sub><br>Thread |      | h <sub>1</sub> | h <sub>2</sub> | s<br>Square | t<br>min. |
| 55       | B 6                         | M 6                      | M 8  | 33             | 22             | 14          | 12        |
| 67       | B 8                         | M 8                      | -    | 37             | 25             | 16          | 16        |
| 80       | B 8                         | M 8                      | M 10 | 41             | 26             | 20          | 16        |

### Specification

- Aluminum
  - Plastic coated
    - black, RAL 9005, textured finish
    - silver, RAL 9006, textured finish
  - blank
- ISO-Fundamental tolerances → Page 1479
- RoHS compliant



### Information

T-Handles GN 563.2 can be used as either operating handles or for clamping purposes, producing high clamping forces.

T-Handles are produced using a stamping process which yields a high density material of high strength and a smooth surface.

An original ELESA-Design, produced in metal with permission of ELESA s.p.a.

see also...

- T-Handles GN 563 (Plastic) → Page 68

| How to order      |  | 1 | Length l                         |
|-------------------|--|---|----------------------------------|
| GN 563.2-67-M8-SW |  | 2 | d <sub>1</sub> (d <sub>2</sub> ) |
|                   |  | 3 | Finish                           |