




Type H Semi-spherical, Steel						
d ±0,05	l ₀	h	l ₁	l ₂	F ₁ Spring load in N ≈	F ₂ Spring load in N ≈
2,2	16	7,8	12	10,5	2,2	3
2,6	8	3,8	6,5	5,2	1,1	2
3	12	6	9	8,7	6,2	6,8
3	16	8,5	13	10,7	4,8	8,4
3,4	12	6	9	7,8	5	7
3,4	15	7,3	12	8,2	5,9	13,3
4	14	8	12	9	5	12,3
5	16	8	13	10,4	8	15

Type HN Semi-spherical, Stainless Steel						
d ±0,05	l ₀	h	l ₁	l ₂	F ₁ Spring load in N ≈	F ₂ Spring load in N ≈
3	16	8	13	4,8	10,6	8,6
3,6	18	9	15	6,7	11,5	14,5
4	16	7,5	13	8	11,4	12,3

Type K Pointed nose						
d ±0,05	l ₀	h	l ₁	l ₂	F ₁ Spring load in N ≈	F ₂ Spring load in N ≈
2,2	16	7,8	12	2,2	12,5	3
3	11	5	9	1,6	6,7	3,4
3	16	8,5	13	4,8	10,7	8,4

Specification

- Housing
 - Type H / K
 - Steel, nickel plated
 - Type HN
 - Stainless Steel AISI 305
- Spring
 - Stainless Steel AISI 301
- *Stainless Steel characteristics → Page 1489*
- RoHS compliant

Information

GN 610 spring loaded shells are used for indexing and locking. A special feature is their large spring travel with a compact size.

A simple hole is sufficient for installation. Pre-tensioning and securing of the spring loaded shells must be ensured by the opposing stop piece.

How to order		1	d
GN610-3,4-15-H		2	l ₀
		3	Type