



- 3 Type**
- R1** Right hand thread, single shaft end
 - R2*** Right hand thread, two shaft ends
 - L1*** Left hand thread, single shaft end
 - L2*** Left hand thread, two shaft ends

d₁	l₁ Travel (Adjustable stroke of the slider) Standard length					Shaft thread	b	d₂	d₃**	d₄***	d₅	d₆	for screw DIN 912
18	100	150	200	250	420	TR10x3	28	6	-	M 5	5,3	-	-
30	100	150	200	300	1500	TR14x4	50	8	M 6	M 6	6,5	9	M 5
40	100	150	200	300	2650	TR20x4	60	12	M 8	M 8	8,5	13,5	M 6
50	100	150	200	300	2760	TR20x4	72	12	M 10	M 8	8,5	13,5	M 8
60	300	400	500	-	2740	TR25x5	80	14	M 10	M 10	10,5	13,5	M 8

d₁	d₇	for screw DIN 912	h₁	h₂	h₃	h₄	h₅	l₂ Total length	l₃	l₄	m₁	m₂	m₃	m₄
18	-	-	28	29	1	14,5	0,75	3xb+l ₁	81	16	2xb+l ₁	68	-	20
30	10,5	M 6	52	54	2	27	0,85	3xb+l ₁	130	16	2xb+l ₁	114	92	30
40	13,5	M 8	60	63	3	31,5	1,05	3xb+l ₁	180	17	2xb+l ₁	160	132	39
50	13,5	M 8	72	76	4	38	1,2	3xb+l ₁	206	18	2xb+l ₁	184	150	46
60	16,5	M 10	86	88	2	44	1,35	3xb+l ₁	240	19	2xb+l ₁	216	185	55

d₁	m₅	m₆	m₇	m₈	m₉	s Hexagon	Key DIN 6885	Installation kit	Position indicator	Handwheel	
18	-	20	18	-	4,5	8	A2x2x12	GN 491.1	GN 955	-	GN 923.18
30	35	30	42	9,5	12	10	A2x2x12	GN 491.1	GN 954	GN 9054	GN 923.30
40	38	39	62	12,5	12	13	A4x4x12	GN 491.1	GN 953	GN 9053	GN 923.40 / GN 924.40
50	50	46	62	13	15	13	A4x4x12	GN 491.1	GN 953	GN 9053	GN 924.50
60	60	55	74	14	16,5	17	A5x5x16	GN 491.1	GN 953	GN 9053	GN 924.60

*** usable depth of thread min. 1,5 x d₄ ** usable depth of thread from both sides min. 2 x d₃ * normally not available from stock