



1 d ₁	2 d ₂		3 l ₁ ±0,5	b	h	l ₂	l ₃	l ₄	t min.	
									M6	M8
30	M 6	M 8	200	18	60	230	170	265	12	15
30	M 6	M 8	250	18	60	280	220	315	12	15
30	M 6	M 8	300	18	60	330	270	365	12	15
30	M 6	M 8	350	18	60	380	320	415	12	15
30	M 6	M 8	400	18	60	430	370	465	12	15
30	M 6	M 8	500	18	60	530	470	565	12	15
30	M 6	M 8	600	18	60	630	570	665	12	15

Specification

- Tube Ø 30 x 1,5
Aluminum / Stainless Steel
 - Handle legs / cover caps
Plastic (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 100 °C
 - Tube aluminum
plastic coated
black, RAL 9005, textured finish ● **SW**
Handle legs / cover caps, black, matt
 - Tube aluminum
anodized, natural color ● **EL**
Handle legs / cover caps, black, matt
 - Tube aluminum
anodized, natural color ● **ELG**
Handle legs / cover caps, light grey, matt
 - Tube Stainless Steel AISI 304
ground, matt shiny finish ● **NG**
Handle legs / cover caps, black, matt
 - *Stainless Steel characteristics* → Page 1489
 - *Load rating information* → Page 1457
 - **RoHS compliant**
- On request**
- Cleanline version (CL)

Information

Owing to their large range of variants and their classic design, GN 666 tubular handles are the perfect choice for many applications.

With the modular structure, special lengths are available even in comparatively small unit quantities. Large handle lengths can be supplied with additional centre struts.

see also...

- *Product family Cleanline* → Page 17
- *Tubular arch handles GN 666.4 (Mounting from the back)* → Page 148
- *Stainless Steel-Tubular handles GN 666.5 (Mounting from the back)* → Page 150

How to order (Tube aluminum)				1	d ₁
1 2 3 4				2	d ₂
GN 666-30-M8-500-EL				3	l ₁
				4	Material / Finish

How to order (Tube Stainless Steel)				1	d ₁
1 2 3 4				2	d ₂
GN 666-30-M8-350-NG				3	l ₁
				4	Material / Finish