




1	2		3						
d ₁	d ₂		l ₁ ±1	b	h	l ₂	l ₃	l ₄	t min.
30	M 6	M 8	400	22	90	440	360	480	15
30	M 6	M 8	500	22	94	540	460	580	15
30	M 6	M 8	600	22	98	640	560	680	15

Ausführung

4

- Handle tube Ø 30 x 1,5
Aluminum / Stainless Steel
- Handle legs
Aluminum, plastic coated
- Cover caps
Plastic (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 100 °C
- Tube / Handle legs aluminum **SW**
plastic coated
black, RAL 9005, textured finish
Cover caps, black, matt
- Tube aluminum **EL**
anodized, natural color
Handle legs
black, RAL 9005, textured finish
Cover caps, black, matt
- Tube aluminum **ES**
anodized, natural color
Handle legs
silver, RAL 9006, textured finish
Cover caps, light grey, matt
- Tube Stainless Steel **NG**
AISI 304
ground, matt shiny finish
Handle legs
black, RAL 9005, textured finish
Cover caps, black, matt

- *Stainless Steel characteristics* → Page 1489
- *Load rating information* → Page 1457

• RoHS compliant

Information

With their curved type, GN 666.4 tubular arch handles highlight modern-machine design.

The production method used allows special solutions to be realised, e. g. with other radii of curvature or other leg heights.

see also...

- *Tubular handles GN 666 (Mounting from the back)* → Page 146

How to order (Tube aluminum)	
1	d ₁
2	d ₂
3	l ₁
4	Material / Finish
GN 666.4-30-M6-500-EL	

How to order (Tube Stainless Steel)	
1	d ₁
2	d ₂
3	l ₁
4	Material / Finish
GN 666.4-30-M8-400-NG	