



- 2 Type**
- ASD** Clamping by turning handle counter-clockwise
 - ASS** Clamping by turning handle clockwise

1

Size	F _H in N Holding capacity	a	b	d ₁	d ₂	d ₃	d ₄	h ₁ ≈	h ₂
50	800	10	17,5	6,5	M 4	12	4,3	45,2	30,5

Size	l ₁ ≈	l ₂ ≈	l ₃ ≈	l ₄ ≈	m ₁	m ₂	m ₃	t min.	w Stroke
50	73	64,5	33	21	16	16	8	9	16

Specification

- Parts in sheet metal
 - case-hardened Steel C10
 - zinc plated, blue passivated
- Plunger
 - Steel St 37
 - zinc plated, blue passivated
- Plunger guide bushing
 - Steel St 37
 - zinc plated, blue passivated
- All moving parts
 - lubricated with special grease
- Hand grip
 - High quality, oil resistant, red plastic
- **RoHS compliant**

Accessory

- Spindle assemblies → Page 585 ff.

Information

GN 840 push-pull type toggle clamps are known for their extremely low height regardless of the position of the operating handle.

see also...

- General information for toggle clamps → Page 500

How to order

GN 840-50-ASD

1 Size

2 Type